

**HIGH POWER
DIODE LASER**

755+808+1064nm
For all skin and hair types

Newest!

Learn more details

□□□□□

.□□□ 16——8 □□□□□□□□ □□□□□□□□ □□□□□□□□ □□□□□□ □□□□ □□□□ *

.□□□□□□□□ □□□□□□ □□□□ □□□□□□ □□□□□□ 3 □□ □□□□ □□□□□□ □□□□□□ 50 □□ □□□□ *

□□□□□□□□ □□□□□□□□ □□□□□□ 1 □□ 3 □ □□□□□□□□ 755 □□□□□□□□ 808 □□□□□□□□ 1064 □□□□□□ 3 *







DIODE LASER

755/808/1064nm diode laser, for all type skin hair removal, painless



ADVANTAGE

- **PAINLESS:** 755/808/1064nm diode laser for all type skin hair removal
- **FASTER:** Large area spot sliding operation
- **NO TRAUMA:** There is no trauma to skin tissue
- **SAFETY:** To avoid the light of the deputy to reduce the difficulty of operation



□□□□□□ □□□

1200 □□□□ □□□□□□□□ □□□□ □□□ □□□ 1800 □ □□□

□□□□□□ □□□ □□□ 35 * 12 □□ 20 * 12

350 *

350 *



800/1000/1200/1600W

50 Million Shots

USA / Germany Imported Laser Bar

755nm+808nm+1064nm



ALEX 755nm
For white skin
(fine, golden hair removal)



SPEED 810nm
For yellow neutral skin
(brown hair removal)



YAG 1064nm
For black skin
(black hair removal)




• *Cooling effect* •

The handle is frosted for one minute,
making your treatment more comfortable and painless



Suitable for hair removal on any part of the body,
Such as arms, legs, face, armpits, back, chest, etc.





-



808 30 □□□□

800 000 16 ---- 8 000 000 000 000 000 000 000 / 000 000 00 000 000 000
000 1600 ---- 000

14 4 □□□□K □□□□□□ □□□□ □□□□

808nm 755 nm 808nm 1064nm

50 □□□□ □□□□

10 ~ 150 ㎜ ㎜ ㎜ ㎜ ㎜ ㎜ ㎜ ㎜ 2 ㎜ / ㎜

1-10 □□□□

0000000 0000000 000000 TEC 0000000 0000000 0000000 0000 00000000 0000000
 00000000 0000000 0000000000 0000000 0000000 0000000 0000 00 000000000

3500

12 * 20 35 * 12

110 〇〇〇〇〇〇〇〇 〇〇〇〇 50 / 〇〇〇〇 220 〇〇 〇〇〇〇 60 / 〇〇〇〇

95 □□□

105 □□□

!በሰዓት በሰዓት የሰዓት ሰዓት በሰዓት የሰዓት ሰዓት በሰዓት
በሰዓት በሰዓት በሰዓት **24 !!**