



*IPL A6*  
 For hair removal  
 & skin rejuvenation

1. 50 \* 15 cm treatment area  
 2. 30,000 - 150,000 pulses  
 3. LCD 8.4 inch TFT touch screen  
 4. Emergency Switch  
 5. Key Switch



000000 000

# Elight Handle Design



## Specification

**Optional Spot Size:**  
15\*50mm

**Imported UK lamp**

**Long shots time:**  
150,000--300,000 times

**7filters:**  
420/510/560/585/640/690/755nm

**Super cooling system**



□□□□□□ □□□□ □□□□□ □□□□□ □□□□□ □□□□ □□□□ □□□□.



□□□□ □□□ □□□□□ □□□□ **8.4** □□□□ □□□□□ □□□ □□□□ □□□□

1. 8.4 □□□□□ □□□□□ □ □□□□□ □□□□ □□□□ □□□□ □□□□

- .2 . /
- .3 .
- .4 OEM ( / )...

# Screen interfac

## Professional Screen, Easy operation



**Main Menu**  
8.4 inch true color big touch screen  
Super cool touch Experience.



**IPL mode:**  
5 options for skin treatment




**IPL mode:**  
operation interface



**Multi-language screen:**  
6 languages for your choice



**System setting**



**System setting**

□□□□ □□ □□□□□□

□□□□□

□□□□□□ □□□□□

□□□□

□□□□

□□□□□□□ □□□□

□□□□

□□□□□

□□□

□□□□

□□□□□□□

IPL: 15 \* 50 □□□□□□ □□□□□□ □□□□ □□□□

420/510/560/585/640/690/755 □□□□□□□□

150.000 □□□□ 30.000 □□□□

□□□□ 8.4 □□□□□□ □□□□ □□□□□ □□□□

1200 □□□□ TEC Cooling Air Cooling Water Cooling 3 in 1 system

2 □□□□□ □□□□

□□□□ 220 □ □□□□ 110 □ □□□□□□□ □□□□□□□ □ □□□□□□□ □ □□□□□□□ □ □□□□□□□ □□□□□□□□

30 □□□□

□□□□□□ □□□□□□ □□□□

□□□□□ □□□□ □□□□ □□□□

## Multi-angle display



Left view



Front view



right elevation