



Free to be yourself

A minute of painless freezing hair removal,
Feeling the comfort and coolness that
has never been seen before.

14-inch screen

2 year warranty + work 24 hours

One minute cooling -21°C



Best **TEC Cooling** system hair remover laser

* ()
(.)
. 3 40 *
1064 808 755 *nm

1000W □ 1200W □ 1600W
12 * 20 □ □ 35 * 12 □ □

350g lightweight **handle**, more ergonomic



Available in **black or white**




High-quality
laser bars
imported from
USA

1000/1200/1600ww high power



Fast hair removal



▶ 10bar
1000W




▶ 12bar
1200W



▶ 16bar
1600W

For all skin types



755nm / 808nm / 1064 nm





14 0000 0000 0000 0000 0000 1064 808 755 00 000000 000000 0000 0000 0000
* 000000 000000 000000 000000 000000 000000 0000
* 00000000 0000 00
* 00000000 0000 0000
* 00000000 000000 0000

The new 14-inch screen is clear
easy to operate.



OEM/ODM SEVRICE

3D LOGO with luxurious texture.