

Free to be yourself

A minute of painless freezing hair removal,
Feeling the comfort and coolness that
has never been seen before



1 Minute
and you're done!

Different spot size Handle color optional



12*20mm



12*35mm



12*20mm



12*35mm

□□□□□□□□ □□ □□□□□□□□

1) 10 .□□□□ □□□□□ 40-10 □ □□□□□ 16 / □□□□ 12 / □□□□

.□□□□□□ □□□□□ □□□□□ □□ 38 * 12 / □□ 20 * 12 □□□□□ □□□□□ (2

.□□□□□□ □□□□□□□ □□□ □□□□□ □ □□□□□□ □□□□ □□□□□ □□□□□ (3

□□□□□ □□□ □□□□□ □□□□□□ □ □□□□□□ □□□□□□ □□□□□ □□□□□□□□ □□□□□□□□ (4.


808 Hair Removal treatment pictures




□□□□□

3 755 □□□□ □□□□ □□□□□nm 808nm 1064nm □ □□□□□□ □□□□□□□ □□□□□□ □□□□□ □□□□□□.


-  755 nm for white skin (fine, golden hair removal);
-  808nm for yellow neutral skin (brown hair removal);
-  1064nm for black skin (black hair removal)



A natural



B energy absorbed by hair



C hair follicle died

Treatment effect



Hair in the treatment area can be easily pulled out



Before



After




Before



After



Before



After

Before





Packing

safe and thoughtful packaging service



Built-in prevention Collision bubble

Two-year warranty for machine handle as consumable,
one-year warranty.

OEM&ODM service for distributor.

Tight packaging

Training: (Video+Manual+Online Service)
Can Keep You Operate It Easily.



3-5 business days delivery

Professional guide:
24 Hours Professional online customer service,



1. 明光科技:

明光科技 是一家专业从事 包装 设备 研发 生产 销售 服务 的高新技术企业。 13 年来 明光科技

Company advantage

Service users all over the world



2.OEM / ODM

- >> OEM
- >> OEM
- << OEM
- <<

Custom Section


CASE design



LOGO design



SYSTEM design




3-□□□□□ □□ □□□ □□□□□□□ □□□□ □□□□

RESEARCH AND DEVELOPMENT

Weifang Mingliangkj electronics Co., Ltd

We have professional Production R & D department, From design research and development to production, every step is strictly checked to ensure product quality.



4. 認證證書展示

