



# Faster, Permanent !

0000000000 00000000 00000000 00000000 00000000 0000 000000 000000

1. 00000000 00000000 0000 0000 00 00000000 00 000000 15 00 0000 000000 .000000.
2. 0000 000 0 00000000 00000000 000000 000 00000000 0000 00 .000000000.
3. 000 0000 000000 000000 0000 000 0 0000 000000.
4. 00000000 000000 000000 000000 0 000000000 1064 000000000 808 000000000 755 :000000000 00000000 00000000 .000000000  
00000000 000000000 00000000 00000000 00000000 000000 00000 0.
5. 0000 000000 000000 0 0000 0000 000000 00000000 0000 0 0000 000000 50 0 000000000 00000000 0000 .0000000 00000  
00000.

00000000 0000

# 12\*24mm or 12\*36mm handle

Suitable for any unwanted hair on areas like face, arms, armpits, chest, back, bikini, legs...



- >>> Big 20\*12 □□□□□□ □□□mm, 12\*35mm for option
- >>> Laser technology, big power 10bar 1200W, 12 bar 1800W
- >>> 300g handle, light weight, free quick slide treatment



>>> New nose hair treatment head, applicable to small part treatment  
>>> 1 minute refrigeration frosting, painless treatment experience






ALEX 755nm  
**For white skin**  
(fine, golden hair removal )



SPEED 810nm  
**For yellow neutral skin**  
(brown hair removal)



YAG 1064nm  
**For black skin**  
(black hair removal)



## Treatment Effect

This is the clinical result of hair removal  
It takes 3--5 times to realize  
permanently hair removal



- \* 4 K 14 Wavelength Laser.
- \* OEM Laser Machine.
- \* Permanent Hair Removal Machine.

مواصفات آلة إزالة الشعر بالليزر ديود

غرض	عمودي 755 نانومتر 808 نانومتر 1064 نانومتر ليزر ديود
نوع الليزر	شريط ليزر طبي ليزر ديود: 10 بار / 15 بار
قوة كل شريط	طبي مع 120 واط / بار
نظام العرض	بوصة تعمل باللمس اللون الحقيقي 14
الطول الموجي	نانومتر / 755 نانومتر / 1064 نانومتر 808
Spot Size	طبي بقطر 12 * 24 مم / 12 * 36 مم <sup>2</sup>
عمر مقبض الليزر	ما لا يقل عن 40 مليون طلقة
طاقة	(جول / سم 2 قابل للتعديل) حتى 150 جول / سم 2 اختياري 10-150
مدة النبض	قابل للتعديل 30 ~ 400ms
تكرار	هرتز 1.0-10
نظام التبريد	كومبريسور هواء دوران ماء مغلق
التعامل مع القوة	واط / 1200 واط / 1600 واط / 1800 واط 1000
قوة الآلة	واط 4000
مصدر كهربائي	فولت / 50 هرتز أو فولت / 110 فولت / 60 هرتز 220
درجة حرارة الكريستال	درجة مئوية 3 ~ -20
درجة حرارة الآلة	درجة مئوية 24
متطلبات الطاقة	هرتز 60 ~ 50 AC220V / 110V



### OEM ODM:

- .
- .
- .
- .
- .

# Premium OEM Factories

High-performance manufacturing capacity  
R&D capability for customization  
Professional certifications and approvals



Our factory is located in Shenzhen, China, with a total area of 10,000 square meters. We have a complete production line and a professional R&D team. We can provide OEM/ODM services for various electronic products. Our products are widely used in various fields, such as medical equipment, industrial equipment, and consumer electronics. We have a strict quality control system and can provide professional technical support and after-sales service. We are committed to providing high-quality products and services to our customers.

Our factory is located in Shenzhen, China, with a total area of 10,000 square meters. We have a complete production line and a professional R&D team. We can provide OEM/ODM services for various electronic products. Our products are widely used in various fields, such as medical equipment, industrial equipment, and consumer electronics. We have a strict quality control system and can provide professional technical support and after-sales service. We are committed to providing high-quality products and services to our customers.

• We have a complete production line and a professional R&D team.  
• We can provide OEM/ODM services for various electronic products.  
• Our products are widely used in various fields, such as medical equipment, industrial equipment, and consumer electronics.  
• We have a strict quality control system and can provide professional technical support and after-sales service.  
• We are committed to providing high-quality products and services to our customers.  
24!