

Stronger, Faster

×

14-inch HD 4K Screen



000000 000

----- 00000 000000 0000 0 000 0000 00 0 000000 00000 0000 000 0000 0000 0000 00000 00000 0 000000

----- 000000 000000 000000 0000000000 00000 000 00000 00 000 00000 000 000 000 00000 00000000 000000000...

----- 808 0000 000000 00000nm 1064 808 755 00nm 0 0000000 000000 00000 00 0000.

---- 1 00000 00000000 .0000 10-1 000000 .0000 00000 00000 !!! -

NEW



NEW



NEW



.ﺩﺭﺍﺩﺍﺭ ﺍﻧﺪﻭﺯﺍﺵ ﺍﻧﺪﻭﺯﺍﺵ ﺍﻧﺪﻭﺯﺍﺵ ﺍﻧﺪﻭﺯﺍﺵ ﺍﻧﺪﻭﺯﺍﺵ ﺍﻧﺪﻭﺯﺍﺵ ﺍﻧﺪﻭﺯﺍﺵ ﺍﻧﺪﻭﺯﺍﺵ ﺍﻧﺪﻭﺯﺍﺵ
ﺍﻧﺪﻭﺯﺍﺵ 24 ﺍﻧﺪﻭﺯﺍﺵ ﺍﻧﺪﻭﺯﺍﺵ ﺍﻧﺪﻭﺯﺍﺵ ﺍﻧﺪﻭﺯﺍﺵ ﺍﻧﺪﻭﺯﺍﺵ ﺍﻧﺪﻭﺯﺍﺵ ﺍﻧﺪﻭﺯﺍﺵ

Free to be yourself

1 minute of painless hair removal,
Feeling the comfort and coolness that
has never been seen before.

14-inch screen

2 year warranty + work 24 hours



□□□□□□ □□□

350g lightweight **handle**, more ergonomic

Available in **black or white**





} 35mm



before after

Large 3.5cm spot size, and integration of three wavelengths
Hair removal is quick, efficient and convenient




One minute cooling -21°C

Best **TEC Cooling** system
hair remover laser



laser rod imported from America.10million—40million shots.Permanent hair removal




755808 1064nm 10million—40million shots.Permanent hair removal

*.10million—40million shots.Permanent hair removal

(10million—40million shots.Permanent hair removal) 10 * 10 *

10 *bar 12bar 16bar 10 *bar 12bar 16bar 10 *bar 12bar 16bar

* 1600 / 1200 / 1000 10million—40million shots.Permanent hair removal



□□□□□□ □□□□□□

Before and After

Traetment comparison





Customer feedback

Ratings&Reviews



m*****a
Georgia

Supplier Service: **Very satisfied** (5 stars)
On-time Shipment: **Very satisfied** (5 stars)

06 Jan 2021



New design 1600W diode laser 755 808 1064 diode la...



Big hug with Maggie, she is very kindness and professional. Weifang Mingliang Electronics Co., Ltd is the best supplier , with high quality and professional package.

If you also need laser machine, strongly recommend them.

0



A*****
Mexico

Supplier Service: **Very satisfied** (5 stars)
On-time Shipment: **Very satisfied** (5 stars)

01 Jan 2021



New design 1600W diode laser 755 808 1064 diode la...



estoy muy feliz con mi compra, me llevo mi pedido a tiempo con buen empaque, espero que todo marche bien.. Maggy una excelente persona y vendedora espero tener más compras a futuro gracias

0



M*****a

Supplier Service: **Very satisfied** (5 stars)
On-time Shipment: **Very satisfied** (5 stars)

20 Jan 2021



Professional high Power 1600W diode laser hair remo...



super

0



New 14-inch 4K screen



808nm .
* OEM. .
*