

1 minute
and you're done

35mm {

FASTER

1. 14 .

2. 6

3. 6

4. OEM

1064 808 755

16 12 10 8

755nm 808nm 1064nm / 808 nm

0-150 2

1-10

40-800

LCD 14.0 TFT True Color LCD

4000

220 60 / 110 50 /

NW / GW 62 78 /

Custom Section


CASE design



LOGO design



SYSTEM design




□□□□□□ □□

CERTIFICATE DISPLAY



Packing

safe and thoughtful packaging service



Built-in prevention Collision bubble

Two-year warranty for machine handle as consumable,
one-year warranty.

OEM&ODM service for distributor.

Tight packaging

Training: (Video+Manual+Online Service)
Can Keep You Operate It Easily.



3-5 business days delivery

Professional guide:
24 Hours Professional online customer service,

