



- *12bar/16bar diode laser, 1200/1600W power,
- *Big spot size 12*36mm , with 755 808 1064nm in the handle,
- *Use USA Coherent imported laser bar , 40 million shots.



1064 nm 1.3nm 808nm 755nm 3 nm 1 nm
1600 / 1200 / 1000 nm : nm

2. big !!!!!!!!!!!!!!! 35 * 12 20 * 12
 3 Dual- TEC 24
 4



00000 00000000 000000 000000 0000
 .0000000 000000 00 000 000 000000 .0000 00 *
 0 0000000 000000 00 000 000 000000 *
 .000000 0000 *
 0 000000 00000000 00000000 00000000 00000000 *
 .0000000 00000000 00000000 000000 *

□ (□□□□□ □□□□ 800 □□□ □□□□□ □□□□ 10) □□□□ □□□□ □□□□ □□□□ *
20 * 12 !□□□ □□□□□□ 350 □□□□□□ □□□□mm □ 12 * 38mm □□□□□□ □□□□□ □□□ □□□□□ □□!



12*20mm or 12*38 / 450g

One minute} Fast and painless hair removal

One minute} cooling -21°C



□□□□□□□ □□□□:

□□□ □□ □□□□ □□□□□ □□□□ Dual- TEC □

□□□□ □□□ □□□□ □□□□ 24 □ □□□□□ □□□□ □□□□□□□□ □□□ □□□□□ □□□□□□□ □□□□□□.

ICE Plus

ICE Plus is an advanced technology that continuously cools skin and facilitates range-controlled temperature throughout the entire treatment. The ICE Plus cold sapphire tip minimizes epidermal risks while maintaining heat within the dermis where hair follicles are treated.

Temperature remains controlled and constant which contributes to the diode's efficiency.

Patients can now enjoy a completely pain-free, cool and comfortable

One minute cooling -21°C




Three Waves 755nm 808nm 1064nm 755nm Alex (epidermal / dermal) 808nm Speed (dermal) 1064nm YAG (deep dermal / subcutaneous) treatment.

755nm Alex (epidermal / dermal) treatment.

808nm Speed (dermal) treatment.

1064nm YAG (deep dermal / subcutaneous) treatment.



0000 0000



00000000 000

000000 / 000000 000000 000000

0000

0000000 00000 0000000

0000000 00000 0000

0000000 0000 00000

00000000 0000

000000 000000 LCD

000000000 00000

00000000 00000:

00000000 0000:

0000000 0000 00000000 0000000000 00000 000000000 000000 000000 0000 755/808/1064

3000 0 0000

0-150J / 000000000 00000) 2 000

10-800 0 (000000000 00000) 000000 00000

1-10 00000


12 * 35 0000000 ²00 20 * 12 / ²00

10.4 0000TFT True Color LCD 0000000 00000

0000000 000000 00000 TEC

00000 16 00 12 00 10 00000 00000

115 * 59 * 61 000




For You. For Life.

Extensive medical and cosmetic treatments

[More Products](#)

Treatment Comparison



Customer Feedback

We are NO.1 in feedback of real client



○ Belgium 11, Sep, 2020,

Supplier Service: **Very satisfied** (5 stars)
On-time Shipment: **Very satisfied** (5 stars)



2020 Alma Laser Soprano 808nm Hair Removal 755n...



this is the first time I ordered something from Alibaba and thanks to Jason I had a reaaaallllyyy good experience. he gave me all the information/tips about the hair removal machine. the delivery was super fast. and omg the results are amazing !!! (see pictures after one session) i will definitely buy more from Jason!



Very satisfied (5 stars)

Very satisfied (5 stars)

2020 Alma Laser Soprano 808nm Hair Removal 755n...



○ United 07, Oct, 2020

Supplier Service: **Very satisfied** (5 stars)
On-time Shipment: **Very satisfied** (5 stars)



2020 Newest Diode Laser 808 nm Alma Soprano ICE ...



im very happy with the machine. Well packed and the machine is Very easy to navi gate!

Very satisfied (5 stars)

Very satisfied (5 stars)

2020 Newest Diode Laser 808 nm Alma Soprano ICE ...



○ Ukraine 02, Apr, 2020

Supplier Service: **Very satisfied** (5stars)
On-time Shipment: **Very satisfied** (5stars)



12 bar 1200W 3 waves laser hair removal machine



Great seller. The product is as specified. He is very emotional, explains everything, sends photos, videos, if something is not clear. I highly recommend! You can or der safely, do not worry, everything will be fine. Thank you seller for your product a nd support! 🙏🙏🙏

Very satisfied (5stars)

Very satisfied (5stars)

12 bar 1200W 3 waves laser hair removal machine



○ Sweden 02, July, 2020

On-time Shipment: **Very satisfied** (5 stars)
Supplier Service: **Very satisfied** (5 stars)



2020 Double Handles Alma Soprano Titanium Diode L...



I am very happy with my machine 😊😊
To start from the beginning, the whole communication and explanation of transpo rt to how the machine works I am super happy.
Viki has helped me a lot, she is the Best.
I bought a hair remover machine and am very happy with the results that the mac hine gives already after the first treatment.
The machine came very well packed in a box and with instructions from Viki I sta rted working with the machine immediately 🙏
I have made my best purchase ever, will only buy from them machines.
Grateful for all the help and support.
Will buy more machines from her.

Very satisfied (5 stars)

Very satisfied (5 stars)

2020 Double Handles Alma Soprano Titanium Diod



ABOUT US

Shandong Smayer Electronics CO.,LTD

14 Years factory, 2 years warranty, 60000+ customers, 102 countries

14 Years factory, 2 years warranty, 60000+ customers, 102 countries



- High Feedback **Top10 Supplier**
- **OEM & ODM** SERVICE



- 00000000 00000000 0000 000000 0 00000000 000000 0000 00 00000 (0)
- 00000000 00000000 00000000 0000 000000 00000000 00000 0000 000000 00000 (0)
- 00000000 00 000000 00000000
- 00000000 0000 000000 0000 000000 0 00000000 00000 0000 0000 00 0000 (0)
- 0000000000 00000000 00000000 0000000000 0000 0000 00 000000000 00000 0000 (0)
- 0000000 00 00000000 00000000000 00000000 00000 0 00 00000000 00000000000 00000 0000 (00)
- 00000000000 00 00000000 00000 00000000 0 000000 00000 000000 000000 000000 (0)

00000000 000000000000 000000000000 00000000 00000000000 000000 000000 (0).

000000000000

Certificate display

Certificate is the best guarantee for you



customer visit



□□□□□□ □□□□□□

Packing

safe and thoughtful packaging service



Built-in prevention Collision bubble

Two-year warranty for machine handle as consumable,
one-year warranty.

OEM&ODM service for distributor.

Tight packaging

Training: (Video+Manual+Online Service)

Can Keep You Operate It Easily.



3-5 business days delivery

Professional guide:

24 Hours Professional online customer service,