




- SUPER ICE PAINLESS EXPERIENCE
- PERMANENT HAIR REMOVAL
- COMFORTABLE HAIR REMOVAL


3 in 1 all skin type can be used



755 nm for white skin (fine, golden hair removal);



808 nm for yellow neutral skin (brown hair removal);



1064 nm for black skin (black hair removal)

□□□□□□ □□□□□□□□ □□□□ □□□□□□□ □□□□ □□□□ □□□□.

- □□□□□□ □□□□□□ □□ □□□ □□□ □□□□□□ □□□□□□ □□.
- □□□□□□ □□□□□□ □□ □□□ □□□ □□□□□□.
- □□□□□□ □□□□.
- □ □□□□□□□ □□□□□□ □□□□□□ □□□□□□□□
- □ □□□□□□□ □□□□□□ □□□□□□ □□□□□□

TEC cooling system

One minute cooling -21°C

Best **TEC Cooling** system
hair remover laser



මෙම මග් ආලෝක ආලෝකය :ආලෝකය ආලෝක **Dual- TEC** ට ආලෝක ආලෝකය ආලෝක ආලෝකය ආලෝකය ආලෝකය ආලෝකය **24** ට ආලෝකය.

handle weighs only 350g

Available in **black or white**



□□□□ □□ □□□□□ □ □ 35 * 12 □ □ 25 * 15 !□□□ □□□□□ 350 □□□□□ □□ :□□□□□□ □□□□□ □□□ □□□□□!

working principle

Hair removal principle

Make Your Beauty Business More Easier




The laser selectively acts on the melanin in the hair follicle, destroying the hair-growing area

Natural hair loss, prevent regeneration, and achieve the purpose of hair removal

Hair removal also stimulates collagen regeneration, shrinks pores and makes skin firm and smooth



Treatment effect comparison



ICE Platinum Diode 35mm 300W

ICE Platinum Diode 35mm 300W ICE Platinum Diode 35mm 300W ICE Platinum Diode 35mm 300W ICE Platinum Diode 35mm 300W

Model / 型號	755/808/1064
Weight / 重量	3000 g
Power / 功率	0-150J / (max) 2 J
Frequency / 頻率	10-800 Hz (max) 1000 Hz
Size / 尺寸	1-10 cm
Resolution / 解析度	15 * 25 dots 20 * 10 / 2 dots
Display / 顯示	10.4 inch TFT True Color LCD
Material / 材質	TEC
Temperature / 溫度	12 °C 10 °C
Humidity / 濕度	105 * 40 * 40 mm
Dimensions / 尺寸	115 * 59 * 61 mm
Weight / 重量	35 g
Frequency / 頻率	220 Hz 60 / 110 Hz 50 / 100 Hz

Model / 型號

Weight / 重量

About the Shipping

**We can offer the door to door services
by air or by sea** just depend on your actual request.

Such as DHL,UPS,TNT,FEDEX...



safe and thoughtful packaging service



OEM&ODM service for distributor.



00000000 0000:	3 000 0000.
00000000 0000:	000 0 00000 000 00000 00 00000 0000 DHL 0 UPS 0 FedEx 0 TNT 0 000.
00000000:	0000 00 00000000 00000