

Power upgrade

Make your hair removal faster



2000W 1064nm

1.3 1064nm 1064nm 1064nm 1064nm 1 1064nm 3000W 755nm 808nm 1064nm 1064nm

1064nm 1600/1064 1200/1064 1000 1064nm 1064nm :1064nm 1064nm

□□□□□□ □□□□□□ □□ □□□□ :□□□□□□.4

- 00000000 00 000 000 000000 .0000 00
- 00000000 00 000 000 000000
- 00000000 0000.
- 00000000 0000000 0000000 0000000 00000000
- 00000000 0000000 0000000 000000

Our



VS



Other



✓ The screen of the handle does not freeze, and the capacitive screen system is operated by sliding



✓ 350g, smaller and lighter, more convenient for treatment



✓ Customizable single band cooling for one minute, no need to wait during treatment, continuous cooling improves efficiency by 50%



✓ Handle cooling piece×3,It can truly cool down in one minute and work 24 hours a day.



✓ Customer feelings:Good,The treatment has a micro-needle feel and is relatively comfortable.



✓ Treatment without waiting



✗ Controller screen freezes, single-point operation



✗ The industrial handle is large and heavy, which makes the healer tired



✗ The replacement head is easy to get dust and burn out, cooling is slow, and you need to wait during the treatment process.



✗ There is only one handle cooling piece, which takes a long time to cool down. You need to wait for the handle to re-cool during the treatment process.



✗ Customer feelings:Poor,The treatment felt like micro-needle, and there was obvious heat pain I couldn't tolerate it after 20 seconds, so I stopped and started again.



✗ Need to cool again during treatment

TEC 24 。

1 2 3 4 5 6

755nm + 808nm + 940nm + 1064nm

For All Skin Types

□□ 25*15 □□□□ □□□□□ □□□□ □□ □□□□ □□□□□ !□□□ □□□□□ 350 □□□□□ □□□ :□□□□□□□ □□□□□□□□□□ □□ 35*12!

Any time
Any where

You can control the machine

Frequency 7 Hz, Energy 25 J/CM, Pulse 11 ms, 15

MLCS

Ios
Android

MLCS

□□□□ □□□ □□□□ □□□□□ □□□□□ :□□□□ □□□□□□□□ □□□□□ □□□□□ □□□ □□□□□.

MULTI-SCREEN LINKAGE

HANDLE WITH LARGE SCREEN, FREE INTERACTION WITH THE MAIN SCREEN, NO DELAY,
CAPACITIVE SCREEN SYSTEM SLIDING OPERATION



STABILIZE



SMOOTH



HANDLE SCREEN



1064 808 755

755

808

1064



Higher power compressor

Ensure the best cooling effect




20%





New filter

- Double filtering
- Ensure clean water quality
- No need to change frequently



New upgrade
Italian water pump

Lifespan increased by 500%

1. 產品名稱：雙層濾水器
 2. 產品型號：ICE
 3. 產品規格：2000 公升
 4. 產品特點：雙層過濾，確保水質清潔，無需頻繁更換。

產品名稱	雙層濾水器
產品型號	ICE
產品規格	2000 公升
產品特點	雙層過濾，確保水質清潔，無需頻繁更換。
產品尺寸	10-800 mm (安裝尺寸)
產品重量	1-10 kg
產品價格	2000 元

显示屏 LCD 显示屏尺寸	显示屏 LCD 10.4 显示屏 显示屏 TFT
显示屏 显示屏	显示屏 显示屏 TEC
显示屏 显示屏:	显示屏 12 10 显示屏 显示屏
显示屏 显示屏	105*40*40 显示屏
显示屏 显示屏:	115*59*61 显示屏
显示屏 显示屏	35 显示屏
显示屏 显示屏	220 显示屏 60/显示屏 110 显示屏 50/显示屏

显示屏 显示屏 显示屏

显示屏 显示屏 显示屏 显示屏 显示屏 显示屏 显示屏



显示屏 显示屏:	3 显示屏 显示屏.
显示屏 显示屏:	显示屏 显示屏 显示屏 显示屏 显示屏 DHL UPS FedEx TNT 显示屏.

□□□□□□□□:	□□□□ □□ □□□□□□□□ □□□□
-----------	-----------------------