



1. 168 小時 24 小時 隨時隨地 隨時隨地 隨時隨地

1) 隨時 隨地 隨時隨地 隨時隨地 隨時隨地 隨時隨地.

2) 168 小時 隨時隨地 隨時隨地 隨時隨地 G 隨時 隨時

3) 隨時隨地 隨時隨地 隨時隨地 隨時隨地 隨時隨地 隨時隨地 隨時隨地 隨時隨地

4) 隨時 隨時 隨時 隨時

Handle Display

The handle is small and light, weighing as low as 168.8g.
Very light to operate



Machine Display



Left 45°



Positive



Right 45°

Cooling Effect

The handle has a cooling effect that improve treatment comfort.



Just One minute!

Quick cooling down to

-25°C

1) 755 nm 808nm 1064nm

2)

Working Principle

755nm and 808nm and 1064nm , suits for all skin and hair types.



ALEX 755nm

For white skin

(fine, golden hair removal)



SPEED 810nm

For yellow neutral skin


(brown hair removal)



YAG 1064nm

For black skin


(black hair removal)



Screen Display

13.3 inch 4K true color touch screen

The display screen is clear at a glance and easy to operate



6 language for your choice. Super cool touch Experience .

Special language can be added according to your actual requirements.

Your logo also can be added on diode laser screen.

1. 13.3 英寸 触摸屏 分辨率 1920x1080 像素 屏幕 尺寸 13.3 英寸 / female . 触摸屏 分辨率 1920x1080 像素 6 语言 触摸屏 . 触摸屏 分辨率 1920x1080 像素 3 . 触摸屏 分辨率 1920x1080 像素 4 OEM 触摸屏 / 触摸屏) 触摸屏...

We have OEM Services

Serving your needs

The central graphic features a handshake in front of a pink 'BEAUTY SALON' logo. Surrounding this are several panels illustrating OEM services: 'Language System program' with flags and a woman; 'Screen/Machine LOGO' with a machine; 'Colors' with four different colored machines; 'Appearance' with a display of machines; and 'Other customization' with a machine in a carrying case.

□□□□□

Weifang Sunshinekj Electronics Co., Ltd (□□□□□: Mlkj) □□□□□□ □□□□□□ □□ □□□□□□ □□□□□ □□ □□□□□□ □□ □□□□ □□ □□□□ □□ □□□□□□ □□□□□□□□□□

13 Years Laser Beauty Decvice Manuafactor

- High Feedback
Top10 Supplier
- OEM & ODM
SERVICE



13 Years Laser Beauty Decvice
Manuafactor

• High Feedback
Top10 Supplier


• OEM & ODM
SERVICE



Premium OEM Factories

High-performance manufacturing capacity
R&D capability for customization
Professional certifications and approvals

2. 13 Years Laser Beauty Decvice Manuafactor R & D department 13 Years Laser Beauty Decvice Manuafactor R & D department 13 Years Laser Beauty Decvice Manuafactor R & D department



□□□□□ □□□□□

Packing

safe and thoughtful packaging service



Built-in prevention Collision bubble

Two-year warranty for machine handle as consumable,
one-year warranty

OEM&ODM service for distributor.

Tight packaging

Training: (Video+Manual+Online Service)

Can Keep You Operate It Easily



3-5 business days delivery

Professional guide:

24 Hours Professional online customer service