

Stronger, Faster

×

14-inch HD 4K Screen



1064 755808 TEC 3 TEC 3 TEC 3 TEC 3 TEC 3

1. 755808 1064 .TEC 3 TEC 3 TEC 3 TEC 3 TEC 3
2. TEC 3 TEC 3 TEC 3 TEC 3 TEC 3
3. TEC 3 TEC 3
4. TEC 3 TEC 3



14 inch 4K HD screen
High-end atmosphere

Front handle
Easy to move the machine

16Bars 1600W Handle
755+808+1064 for all skin types

5. TEC 3 TEC 3
6. TEC 3 TEC 3
7. TEC 3 TEC 3


12*20mm or 12*35mm handle

Suitable for any unwanted hair on areas like face, arms, armpits, chest, back, bikini, legs...



The new **14-inch 4K** screen

Support system customization



* True Color 4K . 14
* OEM .
*

Treatment Effect

This is the clinical result of hair removal
It takes 3--5 times to realize
permanently hair removal





□□□□□□□□ □□□





High-quality laser bars imported from USA


1000/1200/1600w high power
Fast hair removal



▶ 10bar
1000W



▶ 12bar
1200W



▶ 16bar
1600W

755808 1064nm .

* .

() 40-10 *

10 *bar 12bar 16bar

* 1600 / 1200 / 1000

1064 808 755

16 / 12

100

About Us

We Are 13 Years

Professional high-tech beauty equipment manufacturer in China.

潍坊明亮电子有限公司

坚守客户价值不动摇·让客户满意

坚守员工价值不动摇·让员工成长



Mingliangkj in 2007, Through 13 years ,we have built reliable Production ,Quality Control ,Warehousing and Sale&Service department.

Products around world ,including Europe ,North America, Asia and so on .more than 600 clients in more, than 100 countrys all over the world



Packing

Safe and thoughtful packaging service



Built-in prevention Collision bubble

Two-year warranty for machine handle as consumable,
one-year warranty.

OEM&ODM service for distributor.

Tight packaging

Training: (Video+Manual+Online Service)
Can Keep You Operate It Easily.



3-5 business days delivery

Professional guide:
24 Hours Professional online customer service,

About the Shipping

We can offer the door to door services
by air or by sea just depend on your actual request.
Such as DHL,UPS,TNT,FEDEX...

