

NEW ! Technology



- مميزة آلة إزالة الشعر بالليزر التيتانيوم 1600 واط
يستخدم نظام إزالة الشعر بالليزر ديود ، مناسب لجميع أنواع البشرة لإزالة الشعر. 1064 808 755 .1nm
2. قضبان ليزر ذهبية مستوردة من ألمانيا أو الولايات المتحدة الأمريكية ، بحد أقصى 40.000.000 عمر أطول
يضمن عمل الليزر بشكل مستمر بدون مكيف هواء في الصيف ، 3WTEC. نظام تبريد 1600
4. لا ندبة ، أي آثار جانبية.
5. لا ألم ، 3-5 جلسات إزالة الشعر الدائم ، high power

One minute cooling -21°C



Best **TEC Cooling** system
hair remover laser



12*20mm or **12*35mm** handle

Suitable for any unwanted hair on areas like face, arms, armpits, chest, back, bikini, legs...


12*20mm {



12*35mm {




**NEW !
Technology**




High-quality laser bars imported from USA

1000/1200/1600ww high power



Fast hair removal



▶ 10bar
1000W




▶ 12bar
1200W



▶ 16bar
1600W

For all skin types



755nm / 808nm / 1064 nm

The handle equipped with 3 wavelength: Alex 755nm, speed 808nm and long pulse 1064nm

Speed 808nm: Golden standard wavelength for all hair types

Alex 755nm: Specific effective for blonde hair, fine hair

Long Pulse 1064nm: Specific effective for dark, tanned skin



في 1 نظام. 24 ساعة العمل القدرة 3 TEC نظام تبريد 3 في 1: تبريد الهواء تبريد المياه تبريد
مم / 12 * 35 مم حجم بقعة كبيرة ، تقليل وقت العلاج للأصل 12 * 20 1/5



Large Spot Size

Quick and Comfortable

With large spot size of $1.2 \times 3.5 \text{cm}^2$, for faster treatments and better patient experience.



TEC Plus

Continuous Contact Cooling

TEC is an advanced technology that continuously cools skin and facilitates range-controlled temperature throughout the entire treatment. Patients can now enjoy a completely pain-free, cool and comfortable experience throughout the session.



بوصة شاشة تعمل باللمس بالألوان الحقيقية ، تقدم تجربة لمس رائعة للغاية. 12.4 / 14 *
تم قبوله. ضبط المعلمة على ما يرام. OEM * خدمة
* أضف شعارك ولغتك مجانًا

The new 14-inch screen is clear easy to operate.



OEM/ODM SEVRICE

مواصفات آلة إزالة الشعر بالليزر ديود 1600 واط التيتانيوم

عرض	عمودي 755 نانومتر 808 نانومتر 1064 نانومتر ليزر ديود
نوع الليزر	ليزر ديود ، 10 بار 12 بار / 16 بار
قوة كل شريط	واط / بار 100
نظام العرض	شاشة ملونة تعمل باللمس مقاس 12.4 / 14 بوصة
الطول الموجي	نانومتر / 755 نانومتر / 1064 نانومتر 808
حجم البقعة	مم ² / 12 * 35 مم ² 20 * 12
عمر مقبض الليزر	ما لا يقل عن 20-40 مليون طلقة