

□□□□□ □□□ □□ □ □□□ □□

60000+ CUSTOMERS

Customize the machine according
to customer needs



Obtained multi-way authoritative certification,
product testing certification, product patent authority,



□□□□□ □□□ □□□□□□ □□□□□□□ □□□□□ □□□□ □□□□□□



11/11

* 00000000 00 0000000000 00000000 00000000 Dilas .000000 0000 0000000000
.0000 0000 000000 000 000000 00 000000 3 00 0000 0 0000 000000 40 00 0000 *

808 *nm □□□□□ □□□□□ □□□□ □□□□□□□ □□□□

1800 / 1200 1000 : 1000 *

!□□□□□ □□□□□ □□□ □□□□□□ □□□□□ □ □□ 36 * 12 □□ □□ 24 * 12 □□□□□ □□□□□□ □□□□□ □□□ *

□□□ □□ □□□□ □□□□ □□□□ :□□□□□□ □□□□ * Dual- TEC □ □□□ □□□□ □□□□ □□□□ □□□

.0000 000 0000 0000 24 0 0 00000 0000 00000000

□□□□ □□□□ 40 :□□□□ □□□ *



1. □□□□□ □□□□□

12*24mm or 12*36mm handle

Suitable for any unwanted hair on areas like face, arms, armpits, chest, back, bikini, legs...



2.1200 36 * 12 24 * 12 . 1800 .

* 350

() *




3-

* ()

* □□□□□□ □□□□□□ □□□□□□ □□□□□□ □□□□□□ □□□□□□

① Optional 12*24mm/12*36mm light spot size.

Different spot size meet different body parts hair removal needs .



3 755nm and 808nm and 1064nm , suits for all skin and hair types.

The handle has a cooling effect that improve treatment comfort.



Hair removal comparison

The real picture taken by the customer

Different parts of men and women, as well as different skin colors can have very good hair removal results, they all get a permanent and painless hair removal experience



Before



After Treatment

Hair removal comparison

The real picture taken by the customer

Different parts of men and women, as well as different skin colors can have very good hair removal results, they all get a permanent and painless hair removal experience



Before



After Treatment

4. 14 14 14 14 14 14

1. 14 14 14 14 14 14

14 14 14 14 14 14 6 14 14 14 14 6 14 14 14 14 .2

14 14 14 14 14 14 6 .3

14 14 14 .4 OEM 14 / 14) 14...

New upgrade system

The newscreen is clear easy to operate.



5.OEM / ODM 〇〇〇〇〇〇

- >>OEM your own machine body
- >>OEM your own program software
- >>OEM pretty machine colors
- >>Print your LOGO on machine body and screen
- >>R & D team and Quality inspection Show

Exceeding
Your Expectations

The Most
Professional
Beauty Machine
Customization Service



24-Hour online
After-sales service



15 Years Laser Beauty
Device Manufacturer



OEM Factories
Support customization

6. 專業服務

我們提供專業的技術支持，包括產品安裝、操作培訓、故障排除等。我們的技術支持團隊由經驗豐富的工程師組成，可以為您提供全天候的技術支持。我們還提供專業的維修服務，確保您的設備始終處於最佳狀態。我們的專業服務旨在為您提供最佳的客戶體驗，確保您的設備能夠長期穩定運行。