


Working Principle

Suits for all skin and hair types



- **755nm for white skin** (fine, golden hair removal)
- **808nm for yellow neutral skin** (brown hair removal)
- **1064nm for black skin** (black hair removal)

* 35 * 12 20 * 12
450 *
*


Treatment Effect

This is the clinical result of hair removal
It takes 3--5 times to realize
permanently hair remoavl



□□□□ □□□□ □□□ □□□□□□□□

- 1. 12.4 □□□□□ □□□□ □ □□□□□ □□□□ □□□□□
- □□□□□□□ □□□□□□ □□□□□ □□ □□□□□□ 6 □ □□□□□ □□ □□□□□□ 6 □ □□□□□ □□□□ .2
- □□□□ □□□□□ □□□□ □ □□□□ □□□□□□□□ 6 .3
- □□□□ .4 OEM □□□□□ / □□□□□) □□□□□□□□...




Modo de onda	Modo de onda de radiofrecuencia de onda cuadrada
Modo de onda	16 μ onda 12 μ onda 10 μ onda de onda cuadrada de radiofrecuencia / onda de onda cuadrada
Modo de onda	755 μ onda 1064 μ onda 808 μ onda
Modo de onda	0-150 2 μ / μ
Modo de onda	1-10 μ
Modo de onda	40-800 μ onda
Modo de onda LCD	12 μ onda de onda cuadrada de radiofrecuencia de onda cuadrada
Modo de onda	Modo de onda de onda cuadrada de radiofrecuencia de onda cuadrada de onda cuadrada de onda cuadrada de onda cuadrada
Modo de onda	4000 μ
Modo de onda	220 μ onda 60 / μ onda 110 μ onda 50 / μ onda

RESEARCH AND DEVELOPMENT

Weifang Mingliangkj electronics Co., Ltd

We have professional Production R & D department, From design research and development to production, every step is strictly checked to ensure product quality.



CERTIFICATE DISPLAY



Packing

safe and thoughtful packaging service



Built-in prevention Collision bubble

Two-year warranty for machine handle as consumable,
one-year warranty.

OEM&ODM service for distributor.

Tight packaging

Training: (Video+Manual+Online Service)
Can Keep You Operate It Easily.



3-5 business days delivery

Professional guide:
24 Hours Professional online customer service,

