


Working Principle

Suits for all skin and hair types



- **755nm for white skin** (fine, golden hair removal)
- **808nm for yellow neutral skin** (brown hair removal)
- **1064nm for black skin** (black hair removal)

* 35 * 12 20 * 12
450 *
() *



000000 000

00000 000000 000000000 000 0000 00000

0000 0000

16 0 000 12 0 000 10 0 00000000 0000000000 00000000 000000000 / 00000000 000

000000 00000

755 0000000 1064 00000000 808 00000000

0000

0-150 2 00 / 000

00000

1-10 0000

00000 000

40-800 000000 0000

00000 00000 LCD

12 000000000 000000000 0000000 0000 0000

00000000 0000

000000 000000 000000 00000 00 0000000 00000000 00000000 000000 00000000 0000 00000000 0000

000

4000 000


00000000 0000

220 0000 60 / 0000 110 00 0000 50 / 0000

RESEARCH AND DEVELOPMENT

Weifang Mingliangkj electronics Co., Ltd

We have professional Production R & D department, From design research and development to production, every step is strictly checked to ensure product quality.



CERTIFICATE DISPLAY



Packing

safe and thoughtful packaging service



Built-in prevention Collision bubble

Two-year warranty for machine handle as consumable,
one-year warranty.

OEM&ODM service for distributor.

Tight packaging

Training: (Video+Manual+Online Service)
Can Keep You Operate It Easily.



3-5 business days delivery

Professional guide:
24 Hours Professional online customer service,

