



1.3 10000 10000 10000 1 3 755 808 1064

1600 / 1200 / 1000 : 1000

! 35 * 12 20 * 12 -2

: 3 Dual- TEC

. 24

4.Long life:

:





Different spot size Handle color optional



□□□□□□ □□□□□ □□□□ □□□ □□□□□ □□□□□□□□□□

Alex 755nm □□□□□□□□ □□□□□□□□

□□□□□□□□ □□□□□□□□ □□□□□□□□ 808 □□□□□ □□□□□

□□□□□□□□ □□□□□□□□ □□□□□□□□ 1064 □□□□□□ □□□□□

Treatment effect



□□□□□□□□ □□□□□□□□

1. □□□□ □□□□□ □□ □□□□□ □□ □□□□□ 6 □ □□□□□ □□ □□□□□ 6 □ □□□□□ □□□□□
- □□□□ □□□□□ □□□□ □ □□□□ □□□□□□□ 6 .2
- □□□□□ .3 OEM □□□□□ / □□□□□) □□□□□□□□□□...

