



808 Diode Laser

Big Power: 1000w 1200w 1600w

Triple wavelength: 755nm 808nm 1064nm

For different skin type: white, brown, black

□□□□□□□□ □□□□

Machine Parts



□□□□□□ □□□□
□□□□□□ □□□□

□□□□□□□□ □□□□ □□□□□□□□ □□□□□ □□□□□ □□□□
755 □□□□□□□□ 1064 / □□□□□□□□ 808 / □□□□□□□□

6 000000 0000

000000 00000

000000 0000

000000 0000 000000

00000

000000 0000

000000

0000

0000000000 000000 00000 -29 ~ 5 000000 00000

8 000000000 / 000000000 00 0000000 0 0000 16 / 0000 12 / 0000 10 / 0000000
0000000000 0000000000

800 000 1600 / 0000 1200 / 0000 1000 / 0000

00000 10.4 00000 00000000 0000000 0000 000000

40 000 000000

10 ~ 150 000000000 000000 0 2 00 / 0

10 ~ 300ms 0000000000 000000

1 ~ 10 000000

2500 0000



0000

0 000000 000000000 000000 000000000000 :0000000000 0000000000000000.1

00000 0 0000 16 - 8 0 00000000000 0000000000 0000000000 / 0000000000 00000 000000 :0000000000 .2

000000 00 0 00000000 0000000 0000 00000000 0000 0000000 0 0000000 0000000 00000 0000000 0000 1600-800 .0000000


20 * 12 / 000000000 0000000 0000 :0000000000 0000000000 .3mm / 12 * 35mm 0 10-1 00000000Hz 0

00000 000000

00000 :0000000000 000000 .4 TEC 00000000000 0000000 0000000 00000 00000 0000 0000 0000

00000000 0000

Laser show Handle laser bar optional



808nm 1064nm 755nm

755nm

ND YAG 1064nm: 808nm 755nm

Before and After

Treatment comparison



Product Display



□□□□ □□ □□□□ □ □□□□□ □□□□□□ □□ □□□□!