



# 808 Diode Laser

Big Power: 1000w 1200w 1600w

Triple wavelength: 755nm 808nm 1064nm

For different skin type: white, brown, black

□□□□□□□□ □□□

## Machine Parts



□□□□□□ □□□  
□□□□□□ □□□

□□□□□□□□ □□□□ □□□□□□ □□□□□ □□□□ □□□□  
755 □□□□□□□□ 1064 / □□□□□□□□ 808 / □□□□□□□□

6 000000 0000

000000 00000

000000 0000

000000 0000 00000

0000

000000 000

000000

000

0000000000 00000 0000 -29 ~ 5 000000 0000

8 00000000 / 00000000 00 000000 0 000 16 / 000 12 / 000 10 / 000000  
0000000000 000000000

800 000 1600 / 000 1200 / 000 1000 / 000

0000 10.4 00000 00000000 000000 0000 00000

40 000 000000

10 ~ 150 000000000 00000 0 2 00 / 0

10 ~ 300ms 0000000000 00000

1 ~ 10 00000

2500 000



0000

0 000000 000000000 000000 00000000000 :0000000000 000000000000.1

0000 0 000 16 - 8 0 00000000000 0000000000 0000000000 / 0000000000 00000 000000 :000000000 .2

000000 00 0 000000000 0000000 0000 00000000 0000 0000000 0 0000000 0000000 00000 00000000 0000 1600-800  
.0000000

20 \* 12 / 000000000 0000000 0000 :0000000000 0000000000 .3mm / 12 \* 35mm 0 10-1 00000000Hz 0


00000 000000

00000 :0000000000 000000 .4 TEC 00000000000 0000000 0000000 000000 00000 0000 0000

00000000 000



# Laser show Handle laser bar optional



808nm 1064nm 755nm

755nm

ND YAG 1064nm: 808nm 755nm

# Before and After

Treatment comparison



## Product Display



□□□□ □□ □□□□ □ □□□□□ □□□□□□ □□ □□□□□!