

□□□□ □□□□ 40 :□□□□ □□□ *

Four handheld barcode scanners are shown in a row. The two on the left are black with a gold-colored scanning head, and the two on the right are white with a gold-colored scanning head. They are all standing upright on a white reflective surface against a white background with a faint grid pattern.

□□□□ □□□□ (□□□□□□ □□□□□□) □□□□ □□□□ □□□□□□ □ □□□□□ □□□ □□ *



1. 12*24mm or 12*36mm handle

- * 12*24mm handle 1200W
- * 12*36mm handle 1800W
- * 12*24mm handle 1200W
- * 12*36mm handle 1800W

12*24mm or 12*36mm handle

Suitable for any unwanted hair on areas like face, arms, armpits, chest, back, bikini, legs...




2-12*24mm handle 1200W


1. Alex 755nm laser hair removal

2.Speed Diode 808nm 1064nm 1064nm

3-1064nm 1064nm 1064nm 1064nm 1064nm



3. 1064nm 1064nm



Hair removal comparison

The real picture taken by the customer

Different parts of men and women, as well as different skin colors can have very good hair removal results, they all get a permanent and painless hair removal experience



Before



After Treatment

4.Screen 14寸 14寸 14寸

1. 14 寸 14寸 14寸 14寸 14寸

14寸 14寸 14寸 14寸 14寸 6 寸 14寸 14寸 14寸 6 寸 14寸 14寸 .2

14寸 14寸 14寸 14寸 14寸 6 .3

14寸 14寸 .4 OEM 14寸 / 14寸) 14寸...

5.OEM / ODM 14寸

>>OEM your own machine body

>>OEM your own program software

>>OEM pretty machine colors

>>Print your LOGO on machine body and screen


>>R & D team and Quality inspection Show

6. 14寸 14寸

00 .000000 000000 00 .000000000 000000000 000000000 00 000000000 000000000 000000000 000000 000
000000000 00 00 00 0000 00 0000 .0000000 0000 000000 000000000 0000000 0000000 0000000
00000000 000 0000000 000000000 00 00000000 000000.

SHIPPING

Welcome to visit our factory



In terms of following trade details:

- 1)The shipping cost are based on DHL cost to your country
- 2)Delivery time:3-5 days after receiving payments.
- 3)Payment terms:T/T(bank transfer),Western Union.
- 4)Warranty:2 years for the whole machine
- 5)Warranty Policy:one month guarantee replacement (we bear all shipping cost),2years warranty,lifelong maintenance.
- 6)Packing method: Aluminum box with hard plastic foam.
- 7)Free-training to customers:Free We could offer DVD and User's manual and 10 Hours online service to our customers
- 8)Certifications:CE TUV ISO 13485
- 9)MOQ:1 UNIT
- 10)The quotation here above is valid within 1 month