



1. 40000 0000 000000 000000.

2-40.000.000 000000 0000000000 00000000 0000000000 00 00000000 00 00000000 0000000 000000 000000 000000.

3.000000 0 000000 00000 00000000 00000

4. 000000 000000 000000 00000000 000000 000000

5.14.0 0000000 000000 6 00 0000000000 0000000000 00000000 00000 00000 00000.



---- 0000 000000 40-20 00000 00000 00 00000 0 00000000000 0000000000 0000000000 00 00000000 00000 00000

---- 3 个 二极管 阵列 755 808 1064nm 808 二极管 阵列 808nm

---- 功率 100 瓦 1600 瓦 1200 瓦 1000 瓦 功率 瓦

---- 尺寸 38 * 12 寸 25 * 15 寸 20 * 12 英寸 英寸 英寸

---- 重量 450 磅 重量 重量 重量

---- 重量 重量 重量 重量 重量 重量 重量



MACHINE DETAILS DISPLAY

EXQUISITE DETAIL DISPLAY



□□□□ □□

Three Simultaneous Wavelengths in one Applicator
12mm*20mm / 12mm*35

Mix Laser 755nm+808nm+1064nm
Multiple Laser Wavelengths and Technologies

Alex 755nm
Ideal for range of hair colors

Speed 808nm
Safe for darker skin types


YAG 1064nm
Perfect solution for darker skin

□□□□□ □□□□□ □□□□ □□□ □□□ □□□□□□□□

1.Alex 755nm □□□□□□□□ □□□□□□□□

2.Speed Diode 808nm □□□□□□□□ □□□□□□□□

3-□□□□□□□□ □□□□□□□□ □□□□□□□□ 1064 □□□□□□ □□□□□



- **755nm for white skin** (fine, golden hair removal)
- **808nm for yellow neutral skin** (brown hair removal)
- **1064nm for black skin** (black hair removal)

Parameters



●	10-300ms
●	-27 °C ~ 5 °C
●	10 / 16 / 12 /
●	1064 808 755
●	1000 1600 / 1200 /
●	808 3 755/808/1064

