



□□□□□□□□□□ □□□□□□ □□□□□□

- >>No injury to skin and hair follicle; no risk of scarring.
- >>Instantaneous blasting high laser technology, international standard of production, technical test strictly.
- >>Imported stone Q-switch cassette mechanism, the entire solid laser, without replacing Q-switch.
- >>Painless treatment, little side-effect.



# HANDLE-ADVANTAGE



## specification

- **Multiple choice**  
fixed 1064nm & 532nm, adjustable 1064nm&532nm(adjust 1-7 mm)for tattoo removal,nevus removal etc.
- **Multifunction**  
1320nm for skin rejuvenation
- **Indicator light**  
Dot position is the indicator light position dot more accurate



Adjustable  
532nm



Adjustable  
1064nm



Black doll  
1320nm



Fixed  
755nm



Fixed  
532nm



Fixed  
1064nm



.00 7 000 00 1 00 000000 000 000 0000 000

755 / 0000000 1320 / 0000000 532 / 0000000 1064 0 0000000 0000 0000000 532 / 0000000 1064



# Treatment **Effec**

Tattoo removal

Nevus Ota removal

Eyebrow and eyeline removal

Lipline removal



□□□□□ Paramenters

APPLICATION	1)Tattoo removal 2)Eyebrow embroidery removal 3)Eyeline removal 4)Freckles removal 5)Skin rejuvenation 6)Lipline removal 7)Pigment treatment 8)Whitening
wavelength	1064nm&532nm&755 nm & 1320nm &1064nm(Adjustable )&532nm(Adjustable )
Pulse energy	1-1500MJ/CM
Width of Pulse	0-10ns
Frequency	1-10HZ
Light spot	1-7mm
Power supply:	220V, 6A or 110V, 12A
color	Blue and black color
Packing method	Aluminum Packing
N.W	20kg
G.W	30kg
Machine	35cm*45cm*35cm(L*W*H)
Aluminum box	46*49*60cm(L*W*H)



Plastic foam:6cm



strong and beautiful  
aluminum alloy case



N.W 20KG



G.W 30KG

# Free logo service

