



Vorteil der Diodenlaser-Haarentfernungsmaschine 755 808 1064

- 1) Verwenden Sie einen TEC-Kondensator, dieser hat eine bessere Kühlwirkung. Stellen Sie sicher, dass die Maschine auch im Sommer rund um die Uhr läuft.
- 2) Verwenden Sie eine aus Italien importierte Hochdruckpumpe mit einer um 40.000.000 längeren Lebensdauer
- 3) 2 Filter, 1 Filter zum Enthärten des Wassers, 1 Filter zum Trennen von Verunreinigungen.
- 4) Hohe Leistung 2000 W, starke Energie, gute Haarentfernungswirkung.

MULTI-ANGLE MACHINE DISPLAY



New upgrade 14-inch HD 4K screen
12*35mm big spot size
Optional parameters for different skin types



ADVANTAGE

- **PAINLESS:**755/808/1064nm diode laser for all type skin hair removal
- **FASTER:**Large area spot sliding operation
- **NO TRAUMA:**There is no trauma to skin tissue
- **SAFETY:**To avoid the light of the deputy to reduce the difficulty of operation



Before and After

Treatment comparison



• *Cooling effect* •

The handle is frosted for one minute,
making your treatment more comfortable and painless



Suitable for hair removal on any part of the body,
Such as arms, legs, face, armpits, back, chest, etc.



TECHNICAL PARAMETERS

| | |
|----------------------|------------------------------------|
| Device Name | Diode laser hair removal machine |
| Model Number | V30 single handle 4K |
| Wavelength | 755nm 808nm 1064nm |
| Screen size | 14 inch 4K true color touch screen |
| Pulse Duration | 1-300ms |
| Frequency | 1-10hz |
| Spot size | 12*35mm |
| Energy | 1-150J/cm2 |
| Cooling | Water cooling+Air cooling |
| Voltage | AC220V/110V 50HZ/60HZ |
| Demension of machine | 45.4cm*52.1cm*101cm |
| Package | Aluminum box |
| Warranty | 2 years |

Für weitere Produktinformationen kontaktieren Sie uns bitte rund um die Uhr online!