



Produktbeschreibung



Mini-Diodenlaser-Griff

Spotgröße 14*14mm, 5 Balken 600W

Handle Display

*The handle is small and light, weighing as low as 168.8g.
Very light to operate*



1) Diodenlaser 755 nm 808 nm 1064 nm, Haarentfernung für alle Hauttypen. 2)
Wasserkühlung Luftkühlung Kompressorkühlung für schmerzfreie Haarentfernung.

Cooling Effect

The handle has a cooling effect that improve treatment comfort.



Just One minute!

Quick cooling down to

-25°C

Working Principle

755nm and 808nm and 1064nm , suits for all skin and hair types.



ALEX 755nm

For white skin

(fine, golden hair removal)



SPEED 810nm

For yellow neutral skin

(brown hair removal)



YAG 1064nm

For black skin

(black hair removal)

6⁺ ADVANTAGE

HANDLE OF 808 DIODE LASER DEVICE



No pain



No side
effect



Germany
imported bar



Big spot
15*25mm



super cooling
system



Permanent
hair removal



Before and After


Treatment comparison



Screen Display

13.3 inch 4K true color touch screen

The display screen is clear at a glance and easy to operate



6 language for your choice. Super cool touch Experience .

Special language can be added according to your actual requirements.

Your logo also can be added on diode laser screen.

1. 13,3-Zoll-Touchscreen, humanisiertes Design
2. Männlich/weiblich, Körperteile, 6 Hauttypen zur Auswahl.
3. Englisch Ihre Muttersprache.
4. Kostenloser OEM-Programmservice (Logo/System...)

We have OEM Services

Serving your needs

Language
System
program



Appearance



Screen/Machine
LOGO

Colors



Other
customization





Produktverpackung

Packing

safe and thoughtful packaging service



Built-in prevention Collision bubble

Two-year warranty for machine handle as consumable,
one-year warranty

OEM&ODM service for distributor.

Tight packaging

Training: (Video+Manual+Online Service)

Can Keep You Operate It Easily



3-5 business days delivery

Professional guide:

24 Hours Professional online customer service