


The advertisement features a woman with curly hair on the left and a black laser device on the right. The device has a screen at the top and a '50% OFF' sticker. Text overlays include 'GENES LASER', 'NEWEST COMING, FASTEST STRONGEST, DOUBLE HAIR REMOVAL SYSTEM', '1200W + 1800W TITANIUM COMING', and a 'VIEW MORE' button.

GENES LASER

NEWEST COMING, FASTEST
STRONGEST, DOUBLE HAIR
REMOVAL SYSTEM

1200W + 1800W TITANIUM COMING

VIEW MORE

50% OFF

* 1800 W Hochleistungs-Diodenlaser mit schöner Kühltechnologie, für schmerzlose Haarentfernung!

* Diodenlaser ermöglichen es dem Licht, tiefer in die Haut einzudringen und sicherer als andere Laser zu sein. Da es das Melaninpigment in der Epidermis der Haut vermeiden kann, können wir es für die dauerhafte Haarentfernung aller Farbhaare bei allen 6 Arten von Hauttypen verwenden.

* Geeignet für alle unerwünschten Haare auf Bereichen wie Gesicht, Armen, Achselhöhlen, Brust, Rücken, Bikini, Beinen... Es hat auch die Hauterneuerung.

* Frequenz 1-10hz. schnell behandeln!!! Gerät zur schnellen und dauerhaften Haarentfernung. Schmerzlos!!

Handle display

① Optional 12*24mm/12*36mm light spot size.

Different spot size meet different body parts hair removal needs .



*spot size : 12*24mm*



*spot size : 12*36mm*

② 10bars 1200w / 15bars 1800w. 10million—40million shots.

Effective for permanent hair removal

③ 755nm and 808nm and 1064nm , suits for all skin and hair types.

Cooling effect

The handle has a cooling effect that improve treatment comfort.



*spot size : 12*24mm*





*spot size : 12*36mm*


Waves Laser kombiniert 755 nm 808 nm 1064 nm und eignet sich für alle Haut- und Haartypen

755nm für die Haarentfernung bei weißer Haut (feines/goldenes Haar).

808 nm für die Entfernung gelber (natürlicher) Hauthaare
1064 nm für die Haarentfernung bei schwarzer Haut (schwarzes Haar).
Haarentfernungsgerät mit Diodenlaser

working principle


-  755 nm for white skin (fine, golden hair removal);
-  808nm for yellow neutral skin (brown hair removal);
-  1064nm for black skin (black hair removal)



A natural




B energy absorbed by hair



C hair follicle died

working principle


Triple wavelength laser spots work together



Vorher-Nachher-Effekt-Vergleich

Scope of application

Suitable for any unwanted hair on areas like face, arms, armpits, chest, back, bikini, legs...



CE and TUV CERTIFICATE



**U.S. FOOD & DRUG
ADMINISTRATION**

[Home](#)
[Food](#)
[Drugs](#)
[Medical Devices](#)
[Radiation-Emitting Products](#)
[Vaccines & Blood](#)

510(k) Premarket Notification

[FDA Home](#)
[Medical Devices](#)
[Databases](#)



510(k) | Defenses | Registration & Listing | Adverse Events | Recall

CPR Title 21 | Radiation-Emitting Products | X-Ray Accessories

New Search

Device Classification Name	Crossed Laser Gun
510(k) Number	K090205
Device Name	Medical Grade Laser
Applicant	Wanfang Minghang No 13406, Young Street Zhongshan, CN 261000
Applicant Contact	Li Minghang
Correspondent	Beijing Beifeng Medical Room 912, Building 1 Fangshan District Beijing, CN 102404
Correspondent Contact	May Wang
Registration Number	02414613
Classification Product Code	6061
Date Received	03/02/2009
Decision Date	05/27/2009
Decision	Substantially Equivalent
Regulation Medical Specialty	General & Plastic Surgery
510k Review Panel	General & Plastic Surgery
Y/N	Traditional
Reviewed By Third Party	No
Combination Product	No

Certificate of Compliance

No. 041/2012/EMC/ECR/03
Technical Construction No. 041/2012/10/EMC/02

Certificate's Holder: Welling Minglong Electronics CO., LTD
Floor 3, Welling 2, No.1362, Welling East Street
Welling Community, Ningbo Street, High-tech
Zone, Welling, Guangdong, China.

Certification ECM Mark: 

Product: LASER BEAM DEVICE
Model(s): LASER 1000
Verification to: Standard: EN 60820-1:2006+A2:2011
EN 60820-2:2002/EN 60820-1:2006+A2:2011
Issued to CE Declaration
Issued by Declaration Office of the Government of the Hong Kong Special Administrative Region

Remarks: The product has been verified as a category 2, the product is within the requirement of the certificate mark of CE in accordance to the above listed Standard. The above Compliance mark can be affixed on the product in accordance to the CE mark requirement of its scope and use. The requirement can be found at <http://www.emc.gov.hk>. The Certificate of Compliance can only be checked for validity on the website <http://www.emc.gov.hk>

Declaration: I, the undersigned, hereby declare that the product is in compliance with the CE mark requirement of the product.

CE

Declaration Date (20 December 2012) **Expiry Date (20 December 2015)**

Declaration Signature:  **Declaration Signature:** 

ECM

(1) www.emc.gov.hk (2) www.emc.gov.hk/declaration (3) www.emc.gov.hk/declaration (4) www.emc.gov.hk/declaration


Measurement Systems Certification Body No. 2002
Institute for Testing and Certification
T. Bělá 206, 754 21 Zlín, Czech Republic
www.itc.cz

CERTIFICATE
No. 10 0144 SJ

We confirm on the basis of a performed audit that company

Weifang Mingliang Electronics Co.,Ltd.
338Wang Fang Dongjia Street Wafang Circle
Company Reg. No.: 3107000000000

has implemented and documented a functional quality management system
in compliance with the requirements of the standard

EN ISO 13485:2003

Covering the following activities:

**Design & Development, Production and Distribution of IP, Phototherapy System,
Model: VAG-G Switched Laser and RF Device**

The Certificate is based on the basis of the results mentioned in Audit Report No.
2010000000000. The Certificate validity is conditioned by positive results of surveillance audits
which the certified company undertakes in regular




Date of issue: 01.01.2010
Valid until: 31.01.2012
Date of the last certification audit: 04.07.2007

By: Pavel Václav
Head of Certification Body



SHIPPING

Welcome to visit our factory



In terms of following trade details:

- 1)The shipping cost are based on DHL cost to your country
- 2)Delivery time:3-5 days after receiving payments.
- 3)Payment terms:T/T(bank transfer),Western Union.
- 4)Warranty:2 years for the whole machine
- 5)Warranty Policy:one month guarantee replacement (we bear all shipping cost),2years warranty,lifelong maintenance.
- 6)Packing method: Aluminum box with hard plastic foam.
- 7)Free-training to customers:Free We could offer DVD and User's manual and 10 Hours online service to our customers
- 8)Certifications:CE TUV ISO 13485
- 9)MOQ:1 UNIT
- 10)The quotation here above is valid within 1 month