

MLKJ

CUSTOMER SERVICE

15 YEARS FACTORY, 2 YEARS WARRANTY, 102 COUNTRIES, 60,000+ CUSTOMERS.

MLKJ—MAKE YOUR BEAUTY BUSINESS EASIER



15 years factory



2 years warranty



102 COUNTRIES



2 years warranty



14 inch
Screen Size



3000W
Input power



1-10HZ
Frequency



755nm 808nm 1064nm
Wavelength

- >>Machine 14-inch large screen
- >>3000W machine Leistung to ensure the treatment effect
- >>1-10 Hz fast Frequenz and 15x25mm Punktgröße ensures faster, smooth and effective treatment
- >>808 single wave or 755nm/808nm/1064nm perfect triple Wellenlängen
- >>Easy to operate Data Base system,can do the treatment by man mode and women mode, auch andere

Körperteile. Um einen sicheren Parameter für neue Bediener zu gewährleisten

>> Long life time More than 40 millions Schüsse gold laser diode module, anti high temperature.

350g lightweight **handle**, more ergonomic

Available in **black or white**



Der Griff wiegt nur 350 g, was für die Behandlung praktisch ist

>>12 pieces or 16 pieces Germany Dilas original laser bars,600/800W/1200W power is capable to meet all demands of hair removal on the whole body;

>>1-10Hz fast frequency and 15x25mm spot size ensures faster, smooth and effective treatment;
 >Super sapphire touch Kühlung system ensures painless and comfortable treatment;

Hair removal principle

Make Your Beauty Business More Easier






The laser selectively acts on the melanin in the hair follicle, destroying the hair-growing area

Natural hair loss, prevent regeneration, and achieve the purpose of hair removal

Hair removal also stimulates collagen regeneration, shrinks pores and makes skin firm and smooth





-  755 nm for white skin (fine, golden hair removal);
-  808 nm for yellow neutral skin (brown hair removal);
-  1064 nm for black skin (black hair removal)

Behandeln Sie eine lange Lebensdauer von 20-40 Millionen Aufnahmen

Geschwindigkeit 808 nm: Goldene Standardwellenlänge für alle Haartypen
 Alex 755nm: Speziell wirksam für blondes Haar, feines Haar
 Langer Impuls 1064nm: Speziell wirksam für dunkle, gebräunte Haut IPL-Shr-Opt-Laser / Nd-Yag- / Alexandrit-Laser-Haarentfernungsmaschine in bester Qualität Preis








Modell	808V27- Diodenlaser
Lasertyp	808 nm Diodenlaser oder 755/808/1064 3 Wellen
Anzeige	14-Zoll-Touchscreen-System
Wavelength	808nm/755/808/1064
shots	20-40 Millionen Aufnahmen
Energie	10~150 j/cm ² , einstellbar
Frequency	1-10HZ
Cooling	Doppelte TEC-Kühlung
Power	3000W
Spot size	12 * 35 mm oder 12 * 20 mm zur Auswahl
Stromspannung	110 V/60 Hz oder 220 V/50 Hz zur Auswahl

Unternehmensprofil

1. Das Unternehmen Weifang Mingliang verfügt über 15 Jahre Erfahrung in der Herstellung von Schönheitsgeräten im Schönheitsinstrument.

Es wurde in 102 Länder verkauft und bedient über 600.000 Institutionen weltweit.
Erleichtern Sie das Schönheitsgeschäft.



2. Unterstützung der Maschinenschale OEM, Maschinensystem OEM, kann Ihr eigenes Logo hinzufügen....

3. Wir haben eine professionelle Produktions-Forschungs- und Entwicklungsabteilung. Die Aluminiumbox-Verpackungsmaschine ist robust und langlebig, mit Sicherheitsschutz und hilft Ihrer Maschine, sicher nach Hause zu kommen!

Packing

safe and thoughtful packaging service



Built-in prevention Collision bubble

Two-year warranty for machine handle as consumable,
one-year warranty.

OEM&ODM service for distributor.

Tight packaging

Training: (Video+Manual+Online Service)
Can Keep You Operate It Easily.



3-5 business days delivery

Professional guide:
24 Hours Professional online customer service,

**Kontaktiere uns jetzt
24 Stunden online!**