



Tragbare Haushaltshaarentfernungsmaschinenvorteile

- 1) zeigen, dass das Gesamtvolumen der Maschine sehr klein ist.
- 2) Der Anzeigegriff ist klein, der 168g Griff ist sehr leicht
- 3) Die Maschine ist ein Kompressor mit hoher Kühlleistung und geringem Rauschen
- 4) Die Maschine ist leicht und leicht zu tragen

Handle Display

The handle is small and light, weighing as low as 168.8g.
Very light to operate



Machine Display



Left 45°



Positive



Right 45°

Mini-Dioden-Lasergriff, Fleckgröße 14 * 14mm, 5 bar 600w

Cooling Effect

The handle has a cooling effect that improve treatment comfort.



Just One minute!

Quick cooling down to

-25°C

1) Diodenlaser 755nm 808nm 1064nm, Haarentfernung für alle Hauttypen

2) Wasserkühlung Luftkühlung Kompressorkühlung, zur Schmerzlose Haarentfernung.

Working Principle

755nm and 808nm and 1064nm , suits for all skin and hair types.



ALEX 755nm

For white skin

(fine, golden hair removal)



SPEED 810nm

For yellow neutral skin


(brown hair removal)



YAG 1064nm

For black skin


(black hair removal)



Screen Display

13.3 inch 4K true color touch screen

The display screen is clear at a glance and easy to operate



6 language for your choice. Super cool touch Experience .

Special language can be added according to your actual requirements.

Your logo also can be added on diode laser screen.

1. 13,3-Zoll-Touchscreen, Humanisiertes Design
2. Male / femal, Körperteile, 6 Hauttypen für die Option.
3. Englisch Ihre Muttersprache.
4. Kostenloser OEM-Programmdienst (Logo / System...)

We have OEM Services

Serving your needs



Unsere Fabrik

Weifang Sunshinekj Electronics Co., Ltd (Abkürzung: MLKJ) ist ein sehr professioneller und experierter Hersteller von Schönheitsgeräten in China, hat 14 Jahre in der Schönheitsbranche

13 Years Laser Beauty Decvice Manuafactor

- High Feedback
Top10 Supplier
- **OEM & ODM**
SERVICE



13 Years Laser Beauty Decvice
Manuafactor

• High Feedback
Top10 Supplier

• OEM & ODM
SERVICE

• High Feedback
Top10 Supplier

• OEM & ODM
SERVICE

• High Feedback
Top10 Supplier

• OEM & ODM
SERVICE

• High Feedback
Top10 Supplier

• OEM & ODM
SERVICE

• High Feedback
Top10 Supplier

• OEM & ODM
SERVICE

• High Feedback
Top10 Supplier

• OEM & ODM
SERVICE

• High Feedback
Top10 Supplier

• OEM & ODM
SERVICE

• High Feedback
Top10 Supplier

• OEM & ODM
SERVICE

• High Feedback
Top10 Supplier

• OEM & ODM
SERVICE

• High Feedback
Top10 Supplier

• OEM & ODM
SERVICE

• High Feedback
Top10 Supplier

• OEM & ODM
SERVICE

• High Feedback
Top10 Supplier

• OEM & ODM
SERVICE

• High Feedback
Top10 Supplier

• OEM & ODM
SERVICE

• High Feedback
Top10 Supplier

• OEM & ODM
SERVICE

• High Feedback
Top10 Supplier

• OEM & ODM
SERVICE

• High Feedback
Top10 Supplier

• OEM & ODM
SERVICE

• High Feedback
Top10 Supplier

• OEM & ODM
SERVICE

• High Feedback
Top10 Supplier

• OEM & ODM
SERVICE

• High Feedback
Top10 Supplier

• OEM & ODM
SERVICE

• High Feedback
Top10 Supplier

• OEM & ODM
SERVICE

• High Feedback
Top10 Supplier

• OEM & ODM
SERVICE

• High Feedback
Top10 Supplier

• OEM & ODM
SERVICE

• High Feedback
Top10 Supplier

• OEM & ODM
SERVICE

• High Feedback
Top10 Supplier

• OEM & ODM
SERVICE

• High Feedback
Top10 Supplier

• OEM & ODM
SERVICE

• High Feedback
Top10 Supplier

• OEM & ODM
SERVICE

Premium OEM Factories

High-performance manufacturing capacity
R&D capability for customization
Professional certifications and approvals

2. Wir haben professionelle Produktion R & DEpartment, kann technischen Support, 2-jährige Garantie bieten können



Produktverpackung

Packing

safe and thoughtful packaging seivice



Built-in prevention Collision bubble

Two-year warranty for machine handle as consumable,
one-year warranty

OEM&ODM service for distributor.

Tight packaging

Training: (Video+Manual+Online Service)

Can Keep You Operate It Easily



3-5 business days delivery

Professional guide:

24 Hours Professional online customer service