



Diode Laser

Permanent hair removal

[Understand more](#)




14 inch
Screen Size



3000W
Input power



1-10HZ
Frequency



755nm 808nm 1064nm
Wavelength


>>Machine 14-inch large screen

>>3000W machine power to ensure the treatment effect

>>1-10Hz fast frequency and 15x25mm spot size ensures faster, smooth and effective treatment

>>808 single wave or 755nm/808nm/1064nm perfect triple wavelengths

>> Easy to operate Data Base system, can do the treatment by man mode and women mode, also different body part. To ensure a safe parameter for new operator
>> Long life time More than 40 millions shots gold laser diode module, anti high temperature.



HAIR REMOVAL 2020

PAINLESS
HAIR REMOVAL

HAIR REMOVAL HAIR REMOVAL

350g lightweight **handle**, more ergonomic

Available in **black or white**

The advertisement features a collage of six women's faces at the top, with a central black box containing the text 'PAINLESS HAIR REMOVAL'. Below this, the text 'HAIR REMOVAL' appears twice on either side of a central graphic. The main graphic shows two handheld laser devices, one black and one white, against a background of a perspective grid. A blue banner above the devices states 'Available in black or white'. The text '350g lightweight handle, more ergonomic' is prominently displayed above the devices.


Der Griff wiegt nur 350 g, was für die Behandlung praktisch ist

>> 12 pieces or 16 pieces Germany Dilas original laser bars, 600/800W/1200W power is capable to meet all demands of hair removal on the whole body;
>> 1-10Hz fast frequency and 15x25mm spot size ensures faster, smooth and effective treatment;

>Super sapphire touch cooling system ensures painless and comfortable treatment

Hair removal principle


Make Your Beauty Business More Easier



The laser selectively acts on the melanin in the hair follicle, destroying the hair-growing area

Natural hair loss, prevent regeneration, and achieve the purpose of hair removal


Hair removal also stimulates collagen regeneration, shrinks pores and makes skin firm and smooth



755 nm for white skin (fine, golden hair removal);



808 nm for yellow neutral skin (brown hair removal);



1064 nm for black skin (black hair removal)

Griff Lange Lebensdauer, 20-40 Millionen Aufnahmen

Geschwindigkeit 808 nm: Goldene Standardwellenlänge für alle Haartypen

Alex 755 nm: Speziell wirksam für blondes und feines Haar

Langer Puls 1064 nm: Speziell wirksam für dunkle, gebräunte Haut, beste Qualität, Preis für IPL-SHR-Opt-Laser/ND-YAG/Alexandrit-Laser-Haarentfernungsmaschine

Export 102 countries+

102 countries, 60,000+ customers

