



Vorteile eines tragbaren Haarentfernungsgeräts für den Haushalt

- 1) Zeigen Sie, dass das Gesamtvolumen der Maschine sehr klein ist.
- 2) Der Displaygriff ist klein, der 168-g-Griff ist sehr leicht
- 3) Die Maschine ist ein Kompressor mit hoher Kühleffizienz und geringem Geräuschpegel
- 4) Die Maschine ist leicht und einfach zu transportieren

Machine Parts



Handle Display

*The handle is small and light, weighing as low as 168.8g.
Very light to operate*



Machine Display



Left 45°



Positive



Right 45°

Mini-Diodenlaser-Griff, Punktgröße 14 x 14 mm, 5 Balken, 600 W

Cooling Effect

The handle has a cooling effect that improve treatment comfort.



Just One minute!

Quick cooling down to

-25°C

- 1) Diodenlaser 755 nm 808 nm 1064 nm, Haarentfernung für alle Hauttypen
- 2) Wasserkühlung Luftkühlung Kompressorkühlung für schmerzfreie Haarentfernung.

Working Principle

755nm and 808nm and 1064nm , suits for all skin and hair types.



ALEX 755nm

For white skin

(fine, golden hair removal)



SPEED 810nm

For yellow neutral skin


(brown hair removal)



YAG 1064nm

For black skin


(black hair removal)



Screen Display

13.3 inch 4K true color touch screen

The display screen is clear at a glance and easy to operate



6 language for your choice. Super cool touch Experience .

Special language can be added according to your actual requirements.

Your logo also can be added on diode laser screen.

1. 13,3-Zoll-Touchscreen, humanisiertes Design
2. Männlich/weiblich, Körperteile, 6 Hauttypen zur Auswahl.
3. Englisch Ihre Muttersprache.
4. Kostenloser OEM-Programmservice (Logo/System...)

We have OEM Services

Serving your needs



Unsere Fabrik

Weifang Sunshinekj electronics Co., Ltd (Abkürzung: MLKJ) ist ein hochprofessioneller und erfahrener Hersteller von Schönheitsgeräten in China, der seit 14 Jahren in der Schönheitsbranche tätig ist

13 Years Laser Beauty Decvice Manuafactor

- High Feedback
Top10 Supplier
- **OEM & ODM**
SERVICE



13 Years Laser Beauty Decvice
Manuafactor



• High Feedback
Top10 Supplier

• OEM & ODM
SERVICE

Premium OEM Factories

High-performance manufacturing capacity
R&D capability for customization
Professional certifications and approvals

2. Wir verfügen über eine professionelle Produktions- und Entwicklungsabteilung, die technischen Support bieten kann. 2 Jahre Garantie



Product Customization Design



Production and Processing



Program Debugging



Machine Debugging



Batch Production



Fine and Safe Packaging

Produktverpackung

Packing

safe and thoughtful packaging service



Built-in prevention Collision bubble

Two-year warranty for machine handle as consumable,
one-year warranty

OEM&ODM service for distributor.

Tight packaging

Training: (Video+Manual+Online Service)

Can Keep You Operate It Easily



3-5 business days delivery

Professional guide:

24 Hours Professional online customer service