



Mit Pikosekundenlaser

- >>No injury to skin and hair follicle; no risk of scarring.
- >>Instantaneous blasting high laser technology, international standard of production, technical test strictly.
- >>Imported stone Q-switch cassette mechanism, the entire solid laser, without replacing Q-switch.
- >>Painless treatment, little side-effect.



HANDLE-ADVANTAGE



specification

- **Multiple choice**
fixed 1064nm & 532nm, adjustable 1064nm&532nm(adjust 1-7 mm)for tattoo removal,nevus removal etc.
- **Multifunction**
1320nm for skin rejuvenation
- **Indicator light**
Dot position is the indicator light position dot more accurate



Adjustable
532nm



Adjustable
1064nm



Black doll
1320nm



Fixed
755nm



Fixed
532nm



Fixed
1064nm



Sechs Köpfe passen die Punktgröße von 1 mm bis 7 mm an.
Einstellbar 1064nm/532nm, fest 1064nm/532nm/1320nm/755nm.

- * Feste 1064/532 nm, die zur Entfernung von Tätowierungen, Lippenkonturen, Augenbrauen, Nävus of Ota und Nagelpilzentfernung verwendet werden.
- * Feste 1320 nm, die für Hautaufhellung, Porenverkleinerung und Hautstraffung verwendet werden.
- * Feste 755 nm, die zum Aufhellen der Haut verwendet werden, entfernen gelbe Haut, Chloasma, Alterspigmente
- * Einstellbar 1064/532 nm für die schnelle Behandlung großer Flächen, Punktgröße 1-7 mm einstellbar.

Screen Display

The display screen is clear at a glance and easy to operate



8.4 inch true color big touch screen. Super cool touch Experience.
Special language can be added according to your actual requirements.
Your logo also can be added on diode laser screen.

Effektvergleich

Treatment **Effec**

Tattoo removal

Nevus Ota removal

Eyebrow and eyeline removal

Lipline removal



Produktparameter

APPLICATION	1)Tattoo removal 2)Eyebrow embroidery removal 3)Eyeline removal 4)Freckles removal 5)Skin rejuvenation 6)Lipline removal 7)Pigment treatment 8)Whitening
wavelength	1064nm&532nm&755 nm & 1320nm &1064nm(Adjustable)&532nm(Adjustable)
Pulse energy	1-1500MJ/CM
Width of Pulse	0-10ns
Frequency	1-10HZ
Light spot	1-7mm
Power supply:	220V, 6A or 110V, 12A
color	Blue and black color
Packing method	Aluminum Packing
N.W	20kg
G.W	30kg
Machine	35cm*45cm*35cm(L*W*H)
Aluminum box	46*49*60cm(L*W*H)



Plastic foam:6cm



strong and beautiful
aluminum alloy case



N.W 20KG



G.W 30KG

Free logo service

