

NEW PRODUCT

*D10*

## Portable Hair Removal Machine

-Convenient and efficient hair removal-



**Depilación láser permanente máquina de depilación láser de diodo  
Alemania 755 808 1064 diodo láser diodo ipl depilación láser**

# Product details

Ultra-thin large screen, cool light strip



## Ventajas

- \* Barra láser importada de EE. UU. o Alemania 10bars/15bars
- \* Más de 50 millones de disparos, más de 3 años no es necesario cambiar el nuevo mango.
- \* 3 ondas 1064nm 808nm 755nm, 3 en 1 se puede usar todo tipo de piel



# Working Principle

Suits for all skin and hair types



**12\*20nm**

755nm Laser  
808nm Laser  
1064nm Laser



- **755nm for white skin** (fine, golden hair removal )
- **808nm for yellow neutral skin** (brown hair removal)
- **1064nm for black skin** (black hair removal)

## Descripción de productos

## Mini Portable

The net weight of the handle is  
about equal to one iphone

**285g**



Ergonomic handle  
It's not tiring to take off

### **Acerca de la manija**

Gran potencia de 1200 W/1800 W para libre elección

Tamaño de punto de 12\*24 o 12\*36 mm

\* Mango médico de 285 g, peso ligero, tratamiento de deslizamiento rápido gratuito

\* Con luz indicadora, para mostrar las condiciones de trabajo (en la máquina y el mango), uso seguro

**1 minuto de glaseado rápido, experiencia de tratamiento cómoda e indolora**

# What can **we do** in **1 MINUTE**

Time for a cup of instant coffee,  
the handle can quickly frost.





800/1000/1200/1600W

**50 Million Shots**

**USA / Germany Imported Laser Bar**

**755nm+808nm+1064nm**



**ALEX 755nm**

**For white skin**

(fine, golden hair removal )



**SPEED 810nm**

**For yellow neutral skin**

(brown hair removal)



**YAG 1064nm**

**For black skin**

(black hair removal)


**7558081064nm, adecuado para la depilación permanente de todo tipo de piel**



Before



After



Before



After




Before



After



Before



After

## Product parameters



Device Name	Diode Laser Machine
Model Number	Diode Laser D10
Wavelength	755+808+1064nm Technology
Screen size	12inch 4K-HD screen
Lifetime	50 Million shots
Pulse Duration	10-300ms
Laser Bar	100w for each one America Coherent Laser Bar
Frequency	1-10hz
Spot size	12x20mm Spot Size
Energy	1-150J
Cooling System	TEC cooling circulation
Power Of Machine	2500W
Voltage	AC220V 50HZ/60HZ
Demension of machine	380mm*460mm*300mm
Package	Aluminum box
Warranty	2 years for machine 1 year for handle

# Packing

safe and thoughtful packaging service



## Built-in prevention Collision bubble

Two-year warranty for machine handle as consumable,  
one-year warranty.

**OEM&ODM service for distributor.**

## Tight packaging

Training: (Video+Manual+Online Service)  
Can Keep You Operate It Easily.



## 3-5 business days delivery

Professional guide:  
24 Hours Professional online customer service,

**¡Servicio en línea 7 \* 24 horas!**  
**¡Bienvenido a consultar!**