

MLKJ

# CUSTOMER SERVICE

15 YEARS FACTORY, 2 YEARS WARRANTY, 102 COUNTRIES, 60,000+ CUSTOMERS.

MLKJ—MAKE YOUR BEAUTY BUSINESS EASIER



15 years factory



2 years warranty



102 COUNTRIES



2 years warranty



14 inch  
Screen Size



3000W  
Input power



1-10HZ  
Frequency



755nm 808nm 1064nm  
Wavelength

>>Machine 14-inch large screen

>>3000W machine Fuerza to ensure the treatment effect

>>1-10 HZ fast Frecuencia and 15x25mm Tamaño del punto ensures faster, smooth and effective treatment

>>808 single wave or 755nm/808nm/1064nm perfect triple Longitud de ondas

>>Easy to operate Data Base system,can do the treatment by man mode and women mode, también diferentes partes del cuerpo. Para garantizar un parámetro seguro para el nuevo operador

>> Long life time More than 40 millions tiros gold laser diode module, anti high temperature.

**350g** lightweight **handle**, more ergonomic

Available in **black or white**





**El mango pesa solo 350 g, lo cual es conveniente para el tratamiento.**

>>12 pieces or 16 pieces Germany Dilas original laser bars,600/800W/1200W power is capable to meet all demands of hair removal on the whole body;

>>1-10Hz fast frequency and 15x25mm spot size ensures faster, smooth and effective treatment;

>Super sapphire touch Enfriamiento system ensures painless and comfortable treatment;



## Hair removal principle

Make Your Beauty Business More Easier



The laser selectively acts on the melanin in the hair follicle, destroying the hair-growing area

Natural hair loss, prevent regeneration, and achieve the purpose of hair removal

Hair removal also stimulates collagen regeneration, shrinks pores and makes skin firm and smooth



- 755 nm for white skin (fine, golden hair removal );
- 808 nm for yellow neutral skin (brown hair removal);
- 1064 nm for black skin (black hair removal)

### Manejar Larga vida útil 20-40 millones de disparos

Velocidad 808nm: longitud de onda estándar dorada para todo tipo de cabello

Alex 755nm: Específico efectivo para cabello rubio, cabello fino

Pulso largo 1064nm: Efectivo específico para pieles oscuras y bronceadas, la mejor calidad, láser ipl shr opt / nd yag / precio de la máquina de depilación láser alejandrita

Modelo	808- láser de diodo
Tipo de láser	Láser de diodo de 808nm o 755/808/1064 de 3 ondas
Mostrar	Sistema de pantalla táctil de 14 pulgadas
Wavelength	808nm/7558081064
shots	20-40 millones de disparos
Energía	10~150 j/cm <sup>2</sup> , ajustable
Frequency	1-10HZ
Cooling	Refrigeración TEC doble
Power	3000W
Spot size	12*35mm o 12*20mm para elegir
Voltaje	110V/ 60HZ o 220V/50HZ para elegir

### Perfil de la empresa

1. La empresa Weifang Mingliang tiene 15 años de experiencia en la fabricación de equipos de belleza. en instrumento de belleza.

Se ha vendido a 102 países y atiende a más de 600 000 instituciones en todo el mundo Facilita el negocio de la belleza.

2. Admite OEM de carcasa de máquina, OEM de sistema de máquina, puede agregar su

propio logotipo....

3. Tenemos un departamento profesional de I D de producción. La máquina empacadora de cajas de aluminio es resistente y duradera, con protección de seguridad, ilo que ayuda a que su máquina llegue a casa de manera segura!

## Packing

safe and thoughtful packaging seivice



### Built-in prevention Collision bubble

Two-year warranty for machine handle as consumable, one-year warranty.

**OEM&ODM service for distributor.**

### Tight packaging

Training: (Video+Manual+Online Service)  
Can Keep You Operate It Easily.



### 3-5 business days delivery

Professional guide:  
24 Hours Professional online customer service,

**Contáctanos ahora  
24 horas en línea!**