



Advantage




Advantage

portable

5 in 1 salon beauty system saving shipping cost 5 handles for slimming, skin tightening, wrinkle removal

Advantage

high power cavitation 300W more effective vacuum head help a lot for supus fat cell 2 years warranty multi-color for option





Cavitation

Frequency:4Mhz Power:150W

Burning explode fat cell



Monopolar RF

Frequency:40khz Power:300W Body shape fat reduction



Big tripolar RF

Frequency:4Mhz Power:150W

Skin tightening lifting wrinkle removal



Small Tripolar RF

Frequency:1Mhz Power:150W

Skin tightening lifting wrinkle removal



Vacuum

Frequency:1MHz Pressure:-90kpa

Slimming Remove surplus fat cell

artículo Cavitación Vacío Máquina de adelgazamiento RF

Pantalla LCD TFT Pantalla táctil a color de 8 pulgadas

Tecnología CavitaciónVacíoRF (RF monopolarRF tripolar)

Cabezal de máquina de cavitación ultrasónica rf

Cabezal de liposucción al vacío

Piezas de mano Cabezal de RF monopolar

Cabezal RF tripolar (grande) Cabezal RF tripolar (pequeño)

Frecuencia de cavitación

40 khz

Potencia máxima de cavitación

300w

RF tripolar 1-10 MHz (frecuencia de salida) 150 vatios (potencia máxima de salida)

Radiofrecuencia

monopilar

1-10 MHz (frecuencia de salida) 150 vatios (potencia máxima de salida)

Presión de vacío 100 KPA

Tamaño de la máquina: 47*31*38 cm

Tamaño del embalaje de la caja de aluminio: 54*43*46cm

Voltaje 220 V CA/110 V CA

NOROESTE. 15KG G. W. 25KG

Treatment before & after compare



Efecto de aplicación y tratamiento:

- >Suitable for 6 different color skin, including the dark skin.
- >The sapphire temperature cools down $0\sim3^{\circ}\text{C}$, clients feel comfortable and painless in whole treatment .
- >Long continuous working time, ensure the works in Clinic/salon use.

AMAZING EFFECT

Before & After



Before

Five weeks later

Eight weeks later





Before



After



Before



After

Free logo service



iConsulte inmediatamente!