



Household A1

Three bands: 755nm/808nm/1064nm

Suitable for all skin tones

Laser painless hair removal

Ventajas de la máquina de depilación doméstica portátil

- 1) Muestre que el volumen total de la máquina es muy pequeño.
- 2) El mango de la pantalla es pequeño, el mango de 168g es muy ligero
- 3) La máquina es un compresor con alta eficiencia de refrigeración y bajo nivel de ruido.
- 4) La máquina es ligera y fácil de transportar.

Machine Parts



Handle Display

The handle is small and light, weighing as low as 168.8g.
Very light to operate



Machine Display



Left 45°



Positive



Right 45°

Mini mango láser de diodo, tamaño de punto 14*14mm, 5 barras 600w

Cooling Effect

The handle has a cooling effect that improve treatment comfort.



Just One minute!

Quick cooling down to

-25°C

1) láser de diodo 755nm808nm 1064nm, depilación para todo tipo de piel

2) refrigeración por agua refrigeración por aire refrigeración por compresor, para una depilación sin dolor.

Working Principle

755nm and 808nm and 1064nm , suits for all skin and hair types.



ALEX 755nm

For white skin

(fine, golden hair removal)



SPEED 810nm

For yellow neutral skin


(brown hair removal)



YAG 1064nm

For black skin

(black hair removal)



Screen Display

13.3 inch 4K true color touch screen

The display screen is clear at a glance and easy to operate



6 language for your choice. Super cool touch Experience .

Special language can be added according to your actual requirements.

Your logo also can be added on diode laser screen.

1. Pantalla táctil de 13,3 pulgadas, diseño humanizado
2. Hombre/mujer, partes del cuerpo, 6 tipos de piel para elegir.
3. Inglés tu lengua materna.
4. Servicio de programa OEM gratuito (logotipo/sistema...)

We have OEM Services

Serving your needs



Nuestra fábrica

Weifang Sunshinekj electronics Co., Ltd (abreviatura: MLKJ) es un fabricante altamente profesional y experimentado de equipos de belleza en China, tiene 14 años en la industria de la belleza

13 Years Laser Beauty Decvice Manuafactor

- High Feedback
Top10 Supplier
- OEM & ODM
SERVICE



13 Years Laser Beauty Decvice
Manuafactor

• High Feedback
Top10 Supplier

• OEM & ODM
SERVICE



Premium OEM Factories

High-performance manufacturing capacity
R&D capability for customization
Professional certifications and approvals

2. Tenemos un departamento profesional de I D de producción, podemos proporcionar soporte técnico, 2 años de garantía



Empaquetado del producto

Packing

safe and thoughtful packaging service



Built-in prevention Collision bubble

Two-year warranty for machine handle as consumable,
one-year warranty

OEM&ODM service for distributor.

Tight packaging

Training: (Video+Manual+Online Service)

Can Keep You Operate It Easily



3-5 business days delivery

Professional guide:

24 Hours Professional online customer service