

Depilación láser de diodo 808nm profesional máquina de depilación láser de diodo 808

* Adecuado para [todo tipo de depilaciones](#).

* [Permanente](#) depilación.

.

2 YEARS WARRANTY

Smart clinic data center

- Large 12*35 spot size for quick treatment
- TEC continuous cooling system
- Single/Two connectors
- Smart clinic data center
- User friendly large screen
- I-VI skin tones and tanned skin

Most important thing

3 combined wavelengths covering the optimal treatment

Painless Proven safety Permanent hair removal . All skin types, even tanned skin



Ventajas de Depilación láser de diodo de 808 nm

- 1) Adecuado para **cualquier zona de depilación** tales como: Cara, brazos, axilas, pecho, espalda, bikini, piernas...
- 2) **Tratamiento rápido**, frecuencia 1-10hz.
- 3) Se adapta a todo tipo de piel y cabello.



Mango láser de diodo de depilación 808nm

- * Barra importada de EE. UU., Energía más estable y fuerte.
- * Larga vida útil, disparos de hasta 40 millones, sin mantenimiento.
- * Tamaño del punto: 10 * 20 mm / 12 * 35 mm * Enfriamiento con hielo, los clientes no sienten ningún dolor, tratamiento de depilación cómodo.
- * Fuerte potencia, 12 bar 1200W, depilación rápida. 10 bar 1000W, 16 bar 1600W también disponibles

Hair removal principle

Make Your Beauty Business More Easier



The laser selectively acts on the melanin in the hair follicle, destroying the hair-growing area



Natural hair loss, prevent regeneration, and achieve the purpose of hair removal



Hair removal also stimulates collagen regeneration, shrinks pores and makes skin firm and smooth

Before



After



Treatment effect



Hair in the treatment area can be easily pulled out



Before


After



Before



After



Before



After

*12,4 pulgadas pantalla grande inteligente

* Varios idiomas disponibles, se puede agregar su propio idioma.

* Salón, Clínica, cualquiera que desee se puede agregar el logotipo.