



Características Picosegundo Láser

- >>No injury to skin and hair follicle; no risk of scarring.
- >>Instantaneous blasting high laser technology, international standard of production, technical test strictly.
- >>Imported stone Q-switch cassette mechanism, the entire solid laser, without replacing Q-switch.
- >>Painless treatment, little side-effect.



HANDLE-ADVANTAGE



specification

- **Multiple choice**
fixed 1064nm & 532nm, adjustable 1064nm & 532nm (adjust 1-7 mm) for tattoo removal, nevus removal etc.
- **Multifunction**
1320nm for skin rejuvenation
- **Indicator light**
Dot position is the indicator light position dot more accurate



Adjustable
532nm



Adjustable
1064nm



Black doll
1320nm



Fixed
755nm



Fixed
532nm



Fixed
1064nm



Seis cabezales ajustan el tamaño del punto de 1 mm a 7 mm.
Ajustable 1064nm/532nm, fijo 1064nm/532nm/1320nm/755nm.

- * Fijo 1064/532 nm utilizado para la eliminación de tatuajes, eliminación de labios, eliminación de cejas, eliminación de Nevus of Ota, eliminación de hongos en las uñas.
- * Fijo 1320 nm utilizado para blanquear la piel, reducir los poros, levantar la piel.
- * Fijo 755 nm utilizado para blanquear la piel, eliminar la piel amarilla, el cloasma, el pigmento de la edad
- * Ajustable 1064/532 nm utilizado para tratamiento rápido de áreas grandes, tamaño de punto ajustable de 1-7 mm.

Screen Display

The display screen is clear at a glance and easy to operate



8.4 inch true color big touch screen. Super cool touch Experience.
Special language can be added according to your actual requirements.
Your logo also can be added on diode laser screen.

Comparación de efectos

Treatment **Effec**

Tattoo removal

Nevus Ota removal

Eyebrow and eyeliner removal

Lipline removal



Tattoo removal

Tattoo removal

Nevus of Ota removal

Tattoo on brow removal

Lipline removal

Lipline removal

Tattoo on brow removal



Parámetros del producto

APPLICATION	1)Tattoo removal 2)Eyebrow embroidery removal 3)Eyeline removal 4)Freckles removal 5)Skin rejuvenation 6)Lipline removal 7)Pigment treatment 8)Whitening
wavelength	1064nm&532nm&755 nm &1320nm &1064nm(Adjustable)&532nm(Adjustable)
Pulse energy	1-1500MJ/CM
Width of Pulse	0-10ns
Frequency	1-10HZ
Light spot	1-7mm
Power supply:	220V, 6A or 110V, 12A
color	Blue and black color
Packing method	Aluminum Packing
N.W	20kg
G.W	30kg
Machine	35cm*45cm*35cm(L*W*H)
Aluminum box	46*49*60cm(L*W*H)



Plastic foam:6cm



strong and beautiful
aluminum alloy case



N.W 20KG



G.W 30KG

Free logo service

