



1.3 1000 1000 1000 1000 1 1000 3 755 808 1064

1000 :1000W/1200W/1600W

! 35\*12 20\*12 .2


.3 Dual-TEC

.24

.4

# Working Principle

Suits for all skin and hair types



- **755nm for white skin** (fine, golden hair removal )
- **808nm for yellow neutral skin** (brown hair removal)
- **1064nm for black skin** (black hair removal)







**Different spot size** Handle color optional



□□□□ □□□□ □□□□ □□ □□□□ □□□□□□□□

□□□□ □□□□ □□□□ □□□□□□□□ 755 □□□□

Speed Diode 808nm □□□□ □□□□ □□□□

Long Pulse 1064nm □□ □□□□ □□□□ □□□□ □□□□

# Treatment effect



000000 000 000000

1. 0000 000 6 0000 0000 6 000 0 000 000000 000000 00000 000  
000 000000 000000 00 000 000000 00000 000000 000000 6 .2  
0000000 000000 .3 OEM 000000/00000) 000000 00...)



