

# Stronger, Faster

×

## 14-inch HD 4K Screen



000000 00000000

----- 0000 000000 0000000 000000 0000 00 00000 00000 0000000 0000000 00 00000 0000000 0000.

----- 00000 0000000000 00000 0000000 00000 0000 0000000000 0000000 0000000 000000 00 0000000000 0000000 00000 0000000...

----- 0000 00 00 00 0000 000000 00000000 00 0000000000 1064 808 755 00 0000000000 808 00000 00000000 00 00000 000000 00000.

----- 1 00000 00 00000 .00000 10-1 00000000 .00000 0000 0000 0000000!!! -

**NEW**



**NEW**





.0000 00000 00 0000 00 00000000 0000 0000 000000 0000000 0000 00 000000 00000000 000000  
000000 000000 24 0000000 00000000 000000 00!

# Free to be yourself

1 minute of painless hair removal,  
Feeling the comfort and coolness that  
has never been seen before.

14-inch screen

2 year warranty + work 24 hours



□□□□ □□□

**350g** lightweight **handle**, more ergonomic

Available in **black or white**





} 35mm



before after

Large 3.5cm spot size, and integration of three wavelengths  
Hair removal is quick, efficient and convenient




One minute cooling -21°C

Best **TEC Cooling** system  
hair remover laser




laser rod imported from America.10million—40million shots.Permanent hair removal



1064 808 755 nm 光の波長は、可視光領域に属する。可視光領域は、約 400 nm から 700 nm の範囲である。

\* 10 \* 12 \* 16 \* Coherent . 40-10 \* 10 \* 12 \* 16 \*

\* □□□ 1600 / □□□ 1200 / □□□ 1000 □□□□ □□□□



□□□□□ □□□

## Before and After

### Traetment comparison





## Customer feedback

# Ratings&Reviews



m\*\*\*\*\*a  
Georgia

Supplier Service: **Very satisfied** (5 stars)

06 Jan 2021

On-time Shipment: **Very satisfied** (5 stars)



New design 1600W diode laser 755 808 1064 diode la...



Big hug with Maggie, she is very kindness and professional. Weifang Mingliang Electronics Co., Ltd is the best supplier , with high quality and professional package.

If you also need laser machine, strongly recommend them.

0



A\*\*\*\*\*  
Mexico

Supplier Service: **Very satisfied** (5 stars)

01 Jan 2021

On-time Shipment: **Very satisfied** (5 stars)



New design 1600W diode laser 755 808 1064 diode la...



estoy muy feliz con mi compra, me llevo mi pedido a tiempo con buen empaque, espero que todo marche bien.. Maggy una excelente persona y vendedora espero tener más compras a futuro gracias

0



M\*\*\*\*\*a

Supplier Service: **Very satisfied** (5 stars)

20 Jan 2021

On-time Shipment: **Very satisfied** (5 stars)



Professional high Power 1600W diode laser hair remo...



super

0



14
 \*
 808
 .
 OEM
 \*