

2021 Salon Queen

Trending Model 1600W Laser
4K Smart Screen


Newest Germany Tech
Super Ice Cooling, Pain-free
Get most comfortable treatment




102



A natural



B energy absorbed by hair



C hair follicle died

□□□□ □□□□□ □□□□ □□ □□□□ □□□□□□□□

□□□□ □□□□ □□□□ □□□□□□□□ 755 □□□□

Speed Diode 808nm □□□□ □□□□ □□□□


Long Pulse 1064nm □□ □□□□ □□□□ □□□□ □□□□

Handle Details


Three Wavelengths Work Together




12*20nm
 755nm Laser
 808nm Laser
 1064nm Laser




12*35nm
 755nm Laser
 808nm Laser
 1064nm Laser



□□□□□ □□□□ □ □□ □□□□□

1. □□□□□□□ □□□□ □□□□ :□□□□ □□□□ US Coherent/ Dilas brand
2. 3 808 □□□□□□□□ 755 :□□□□
1 □□ 3 □□□□□□□□ 1064 □□□□□□□□
- □□□□ 35 * 12 □□□□ □□□□ 20 * 12 :□□□□ □□□□□□□ .3
4. 1000 □□□□ □□□□ :□□□□W 1200W 1600W □ OEM
3. □□□ □□□□□ □□□□ 24 □□□□□□□ 1 □□ □□□□ □□ □□ □□□□ □□□□□ □□□ □□□□ □□□ :□□□□□□ □□□□



□□□ □□□□ □□□□□□□□

□□□□□ □□□ □□□□□ Super TEC □□□□□□ □□□□□□ 1 □□□□□ □□□□□□ □□□

□□□□□□□□□□ □□□□ 22- □□□□ □□□□□□□□

Before and After

Treatment comparison



□□□□□ □□ □□□□□

1. □□□□□ □□□□□ □□ □□□□ □□□ 6 □□□□□ □□□□ □□□□ 6 / □□□□ □ □□□□□ □□□□ □□ :□□□□ □□□□ □□□□□

□□□ □□□□□ □□□□□ □□ □□□ □□□□□ □□□□ □□□□□ □□□□□ 6 .2

□□□□□□ □□□□□ .3 OEM □□□□□/□□□□□) □□□□□ □□...)

