


4. 100000 100000 100000 10000



□ □ □ □ □ □ □ □ □ □ □ □

1. ພື້ນ ພື້ນພື້ນ ພື້ນພື້ນ ພື້ນພື້ນ .ພື້ນພື້ນ ພື້ນ ພື້ນພື້ນ ພື້ນ ພື້ນພື້ນ.
2. ພື້ນພື້ນ ພື້ນ ພື້ນພື້ນ ພື້ນ ພື້ນ ພື້ນ ພື້ນ ພື້ນ ພື້ນ.
3. ພື້ນ ພື້ນພື້ນ ພື້ນ ພື້ນ ພື້ນ ພື້ນ ພື້ນ ພື້ນ

□ □ □ □ □ □ □ □ □ □ □ □ □ □ □ □

How is it different?



The image displays a dental curing unit, the EXFU model, which is a compact, grey device with a blue curing light. The unit features a control panel with a blue circular light and the text "EXFU" and "Curing Light". Several different curing tips are shown next to the unit, including a red one and several black ones. A larger blue and silver curing tip is shown in the foreground.

[illegible]

1. 532: 0000 000 00 0000 000 00000000.
2. 000 00 00000000 00000000 0 00 0 00 000000 0000 000 0000 000 00 0000 :755 0000000 0000 00 0000 00 000 0000
3. 0000 0000 000 000000 00000 000 0000 :1064 000000 00000 00000000
4. 000 00 00000000 0000 00000 000 0 00000000 00000 000 00 0000 :1064 000000 00000 000 00000000
5. 1320: 000 000 0 0000 000000 00000 0000000 00000 000000 000000 000000

[illegible]

3. 0000 0000 000 00000 0000 000 0000 :1064 00000 0000 00000000
4. 000 00 00000000 0000 0000 000 0 00000000 0000 000 00 0000 :1064 00000 0000 000 00000000
5. 1320: 000 000 0 0000 000000 0000 000000 0000 000000 000000 000000

[illegible]

5. 1320: 1000 1000 1 10000 100000 10000 100000 10000 100000 100000 100000

Advantage

The maximum energy, the best effect

Laboratory data shows that the laser rod reaches 2000mj.
Precise calculation of laser value
The aiming distance of the indicator light is 6-10cm

5 treatment heads

Detachable and rotatable outer wire design

532: Remove colored tattoos.

755:honeycomb head: used to remove age spots, freckles, and chloasma. little damage to skin


Adjustable parameter 1064: for tattoo removal, eyebrow clearing

1064: used for removing tattoos and clearing eyebrows

1320: large area treatment, large spot, fast treatment speed and good effect

□□□ □□□□□

Working Principle



TREATMENT HEADS



532: Remove colored tattoos.



755 honeycomb head: used to remove age spots, freckles, and chloasma. little damage to skin



Adjustable parameter 1064: for tattoo removal, eyebrow clearing



1064: used for removing tattoos and clearing eyebrows



1320: large area treatment, large spot, fast treatment speed and good effect

Product Features



Tattoo removal

Eyebrow embroidery removal

Freeline removal

Eyeline removal

Whitening

Skin rejuvenation

Lipline removal

Pigment treatment

1. 2000 毫 瓦 激光 治疗 仪

2. 2000 毫 瓦 激光 治疗 仪 可 达 到 2000mj 毫 瓦 功 率。

3. 2000 毫 瓦 激光 治疗 仪

4. 2000 毫 瓦 激光 治疗 仪 10-6 毫 瓦 功 率 可 达 到 2000mj 毫 瓦 功 率


5. 2000 毫 瓦 激光 治疗 仪

1064nm

Precise Calculation Laser Value

The aiming distance of the indicator light is 6-10cm

6-10cm




You think you can. you can
No one can stop me




Q. 1064nm 레이저는 어떤 질환에 효과가 있는 것인가요?
 레이저는 피부의 색소나 혈관을 파괴하여 제거하는 효과가 있습니다. 레이저를 이용하여 피부의 색소나 혈관을 제거하면, 피부가 깨끗해지고, 피부의 결함도 개선됩니다. 레이저를 이용하여 피부의 색소나 혈관을 제거하면, 피부가 깨끗해지고, 피부의 결함도 개선됩니다. 레이저를 이용하여 피부의 색소나 혈관을 제거하면, 피부가 깨끗해지고, 피부의 결함도 개선됩니다.

Treatment **Effec**

Tattoo removal



Nevus Ota removal



Eyebrow and eyeliner removal



Lipline removal




After





After



After



After



Original pigment

Traditional laser


Picosecond Laser



1. 100% 100%
 2. 100% 100% 100% 10 100% 100% 100%
 3. 100% 100% 100% 100%
 4. 6 100% 100% 100% 100% 100% 100% 100% 100% 100% 100%
 5. OEM 100% / 100% / 100% 100% 100% 100% 100% 100% 100% 100%

Screen Image

The display screen is clear at a glance and easy to operate



10 inch true color big touch screen. Super cool touch Experience.
Special language can be added according to your actual requirements.
Your logo also can be added on diode laser screen.

Picosecond new upgrade

The maximum energy, the best effect

Smallest size

Rational design

5 treatment heads, detachable and rotatable outer wire design
a solution to a variety of skin problems



1. 产品简介

2. 产品特点

3. 技术参数

4. 适用范围

5. 操作说明

6. 维护保养

7. 售后服务

1. 产品简介 / 产品特点 Nd yag

2. 产品特点 产品特点 产品特点 / 产品特点 产品特点

3. 技术参数 5 项

4. 适用范围 1064nm 532nm 1320nm 755nm

5. 操作说明 产品特点 产品特点 产品特点 产品特点....

6. 维护保养 1-10 项

7. 售后服务 110V/220V 50-60Hz

产品特点 产品特点 产品特点

15 项产品特点 产品特点 产品特点 产品特点 产品特点 产品特点 产品特点!

15 项产品特点 产品特点 产品特点 产品特点

产品特点 产品特点 CE 产品特点 产品特点 TUV 产品特点 产品特点 产品特点 产品特点 OEM



15 Years Laser Beauty Device Manufacturer

本公司擁有超過 15 年的經驗，專注於雷射美容設備的研發與生產。我們擁有 126 名專業技術人員，致力於為全球客戶提供高品質、高性能的雷射美容設備。我們的生產能力強大，年產量可達 60000 台。

我們提供多種雷射美容設備，包括雷射脫毛、雷射祛斑、雷射緊膚等。我們的設備採用最先進的雷射技術，具有操作簡單、效果顯著、恢復快等優點。我們的產品已廣泛應用於各大美容院、皮膚科診所及醫療機構，深受客戶好評。我們還提供完善的售後服務，確保客戶使用無憂。

Our Showroom



Our products are designed and manufactured in accordance with the highest standards of safety and efficacy. We are proud to hold CE, FDA, TUV, and ISO 13485 certifications, ensuring that our devices meet the most rigorous international requirements.

Our products are designed and manufactured in accordance with the highest standards of safety and efficacy. We are proud to hold CE, FDA, TUV, and ISO 13485 certifications, ensuring that our devices meet the most rigorous international requirements.

We offer ODM/OEM services, allowing us to customize our devices to meet the specific needs of our clients. Our experienced engineering and manufacturing teams work closely with our clients to develop and produce high-quality, custom-tailored medical devices. We are committed to providing our clients with the most advanced and effective solutions for their medical needs.

CERTIFICATES



BV-France's most authoritative
certification body BV Group certification



TUV-Germany's most authoritative
certification body Rheinland certification



SGS-Switzerland's most authoritative
certification body SGS certification



Italy ECM Certification



ISO 13485

NQA medical system
certification



Production Process



Warehouse spare parts



Parts assembly



Precision machining



Handle fabrication



Product assembly process



Quality inspection
of finished products



Product packaging

本公司是一家专业从事精密机械加工、电子产品组装、精密模具制造、精密零件加工、精密零件检测、精密零件包装、精密零件仓储、精密零件物流、精密零件销售、精密零件服务于一体的综合性企业。公司拥有先进的生产设备、专业的技术人员、完善的质量管理体系、严格的保密制度、快捷的交货周期、合理的价格、优质的服务。公司自成立以来，始终秉承“质量第一、客户至上”的经营理念，为客户提供高品质的产品和服务。公司主要产品有：精密机械加工、电子产品组装、精密模具制造、精密零件加工、精密零件检测、精密零件包装、精密零件仓储、精密零件物流、精密零件销售、精密零件服务。公司欢迎广大客户垂询、合作。

. 公司拥有一流的生产设备、专业的技术人员、完善的质量管理体系、严格的保密制度、快捷的交货周期、合理的价格、优质的服务。公司自成立以来，始终秉承“质量第一、客户至上”的经营理念，为客户提供高品质的产品和服务。公司主要产品有：精密机械加工、电子产品组装、精密模具制造、精密零件加工、精密零件检测、精密零件包装、精密零件仓储、精密零件物流、精密零件销售、精密零件服务。公司欢迎广大客户垂询、合作。

公司地址：深圳市宝安区西乡街道

Packing

Safe and thoughtful packaging service



Tight packaging

The machine shall be made of waterproof materials and packaged

**Anti collision foam board
inside aluminum box**



3-5 business days delivery

Professional guide:

24 Hours Professional online customer service

CONTACT US



In terms of following trade details:

- 1)The shipping cost are based on DHL cost to your country
- 2)Delivery time:3-5 days after receiving payments.
- 3)Payment terms:T/T(bank transfer),Western Union.
- 4)Warranty:2 years for the whole machine
- 5)Warranty Policy:one month guarantee replacement (we bear all shipping cost),2years warranty,lifelong maintenance.
- 6)Packing method: Aluminum box with hard plastic foam.
- 7)Free-training to customers:Free We could offer DVD and User's manual and 10 Hours online service to our customers
- 8)Certifications:CE TUV SFDA ISO 13485
- 9)MOQ:1 UNIT
- 10)The quotation here above is valid within 1 month