

Diode Laser



15 Bar **1800W** Handle

*Increase the treatment head of nasal hair
and treat small parts easily



.00000 0000 000000 0000 0000000
00000 000 00 00000 000000 00000000 00000 *

00000 000 00 00000 000000 *

00000 0 00000 *

.00 000 0000000 000 000000 00000000000 *

808 000000 00000 0000 0000 *nm 7558081064 00nm.

350g

Ultra light handle



12×36mm

Handle

1800W diode laser hair removal




12×24 mm

Handle

1200W diode laser hair removal

이 제품은 350g의 초경량 핸들을 특징으로 하며, 1064nm, 808nm, 755nm의 파장을 지원하여 다양한 피부 타입에 적합합니다.

755nm (피부색/모색에 적합)은 피부색과 모색에 따라 조절 가능하며, 808nm (피부색)은 피부색에 따라 조절 가능하며, 1064nm (모색)은 모색에 따라 조절 가능합니다.






ALEX 755nm
For white skin
 (fine, golden hair removal)




SPEED 810nm
For yellow neutral skin
 (brown hair removal)



YAG 1064nm
For black skin
 (black hair removal)



Treatment Comparison





Emergency
stop button

12 inch big screen
quick touch
easy operate

Diode laser handle

Vents

Plug