

**HIGH POWER
DIODE LASER**

755+808+1064nm
For all skin and hair types

Newest!

Learn more details

□□□□□□

.□□□ □□□ □□□□ □□□ 16--8 □□□□ □□□□ □□□□ □□ □□□□□ □□□□□□ *

.□□□□ □□□□ □□□□ □□□□ □□ □□□□ □□□ 3 □□ □□□ □□□□□ □□□□□□ 50 □□ □□□ *

□□□ □□□□□□□ □□□□ □□□□ □□□ □□□ 1 □□ 3 □□□□□□□□□ 755 □□□□□□□□ 808 □□□□□□□□ 1064 □□□ 3 *





Arm hair removal



Face hair removal



Lip hair removal



Leg hair removal



Back hair removal



Underarm hair removal



Bikini hair removal



DIODE LASER

755/808/1064nm diode laser, for all type skin hair removal, painless



ADVANTAGE

- **PAINLESS:** 755/808/1064nm diode laser for all type skin hair removal
- **FASTER:** Large area spot sliding operation
- **NO TRAUMA:** There is no trauma to skin tissue
- **SAFETY:** To avoid the light of the deputy to reduce the difficulty of operation



□□□□ □□□□□□

□□□□□□ □□□□□□ □□□□ □□ 1800 □□□□ 1200 □□□□ □□□□

□□□ □□□□ 35 * 12 □□ 20 * 12 □□□□ □□□□□□

350 *

*
0000



800/1000/1200/1600W
50 Million Shots
USA / Germany Imported Laser Bar

755nm+808nm+1064nm



ALEX 755nm
For white skin
(fine, golden hair removal)



SPEED 810nm
For yellow neutral skin
(brown hair removal)



YAG 1064nm
For black skin
(black hair removal)



• *Cooling effect* •

The handle is frosted for one minute,
making your treatment more comfortable and painless



Suitable for hair removal on any part of the body,
Such as arms, legs, face, armpits, back, chest, etc.








14 Android Screen

1. Three wavelength diode laser.
2. Golden laser bars from German or USA improved, 40,000,000+ longer lifespan.
3. Safe, Fast, Painless, permanent
4. For all skin and hair style hair removal
5. 14.0 inch true color touch screen with 6 skin colors.



Model

808V30

Power

800 W 16W---8 W 1600W

Wavelength

4 Wavelength 14 Wavelength 808nm 755nm 808nm 1064nm

Fluence

50 J/cm²

Energy

10~150 J/cm²

Grid size

1-10 cm

Time

TEC

Temperature

3500 W

Size

12 * 20 cm

Weight

35 * 12 cm

Power

110 W 50 / 220 W 60 / 220 W

Fluence

95 J/cm²

Energy


105 J/cm²

Premium OEM Factories

High-performance manufacturing capacity
R&D capability for customization
Professional certifications and approvals



Product Customization Design



Program Debugging



Batch Production



Production and Processing



Machine Debugging



Fine and Safe Packaging

! 24 24