

Soprano Ice Titanium

Painless hair removal. For you, for life!



□□□□ □□□□□□ □□ □□ □□□

00000000 808 0000 0000 0000 000000 00000000 00000000 000 0000 000 0000 000 000
00000 00 00000 00

□□□□ □□□□ □□□□ □□□ □ □□□□ □□□ □ □□□□ □□□□ □□□□ □□□ □□□ □□□□ (□□□.

[illegible]

በጥቅም ላይ የዋለው የጥናት ዘመን በጥንቃቄ መመረቅ ይገባል፡፡

[illegible]

በግልጽ በሚታወቅ የሚገኝ የግብርና ስራ ለግብርና ስራው ስራው ስራው ስራው ስራው (፲.

350g

Ultra light handle



12×36mm

Handle

1800W diode laser hair removal



12×24 mm

Handle

1200W diode laser hair removal

808 nm 1800W diode laser hair removal device
36 * 12 / 24 * 12 mm diode laser hair removal
I-VI diode laser hair removal device

Soprano



755

808

1064

3 Wavelengths

New breakthrough!



360 ° Rotatable

6.8×6.8mm

Handle

1200W diode laser hair removal

Improved Reach: **360 ° Rotatable**

Easily treat areas that are normally hard to reach,
including the ears, nostrils and glabella.

□□□□ □□□□□□

Treatment Comparison





000000 0000 000000 000000 00000000
 0000 000 0000000 14 0000 000000 0000 .1
 0000 000 6 0000 0000 6 000 0 000 000000 0000000 000000 000 .2
 000 000000 000000 00 000 000000 0000 000000 000000 6 .3
 00000000 000000 .4 OEM 000/000000/00000/00000) 00000000...)

14inch true touch screen
6 kinds skin type for choice. accept ODM OEM Service.

The new **14-inch** screen is clear easy to operate.



Advantage of: soprano ice laser hair removal machine

Super cooling: air + water+TEC condenser cooling system,
Which keep water temperture in 25-28°C,continuous work in summer.
Germany imported laser: 12 laser bars handle, 10-40 million shots.
Big spot size 15x25mm,12*38mm,1200 w high power to sure fast hair removal.
Italian water pump: more better for the laser water ciculate
Painless and no side effect.



**14 Years
 Laser Beauty Decvice
 Manuafactor**

- High Feedback **Top10 Supplier**
- **OEM & ODM** SERVICE



本公司是一家专业生产各种美容仪器的工厂，拥有14年的生产经验，2年的质保，60000+的客户，102个国家。我们提供OEM和ODM服务。我们的产品包括各种激光美容仪器，如激光脱毛仪、激光点痣仪、激光祛斑仪等。我们的产品品质优良，价格公道，深受客户的欢迎。我们欢迎各界人士前来咨询和订购。

Certificate is the best guarantee for you



Packing

safe and thoughtful packaging service



Built-in prevention Collision bubble

Two-year warranty for machine handle as consumable,
one-year warranty.

OEM&ODM service for distributor.

Tight packaging

Training: (Video+Manual+Online Service)
Can Keep You Operate It Easily.



3-5 business days delivery

Professional guide:

24 Hours Professional online customer service,

CONTACT US



In terms of following trade details:

- 1)The shipping cost are based on DHL cost to your country
- 2)Delivery time:3-5 days after receiving payments.
- 3)Payment terms:T/T(bank transfer),Western Union.
- 4)Warranty:2 years for the whole machine
- 5)Warranty Policy:one month guarantee replacement (we bear all shipping cost),2years warranty,lifelong maintenance.
- 6)Packing method: Aluminum box with hard plastic foam.
- 7)Free-training to customers:Free We could offer DVD and User's manual and 10 Hours online service to our customers
- 8)Certifications:CE TUV SFDA ISO 13485
- 9)MOQ:1 UNIT
- 10)The quotation here above is valid within 1 month