



1. CE ISO13485  
 2. CE ISO13485  
 3. CE ISO13485  
 4. CE ISO13485  
 5. CE ISO13485  
 6. CE ISO13485  
 7. CE ISO13485  
 8. CE ISO13485  
 9. CE ISO13485  
 10. CE ISO13485



1. .  
 2. 35 \* 12 20 \* 12 1200 1000 :  
 3. 10-1 :  
 4. TEC 24

1600 1200 1000

One minute cooling -27°C

# Best TEC Cooling system hair remover laser




.20\*1.12 35 \* 2.12 .3

**350g lightweight handle, more ergonomic**

Available in **black or white**



- >>Germany Emitter, strong
- 1200<<W power of hair removal on the whole body;
- >>1-10Hz fast
- >> Italy water pump, it can keep machine working 24 hours without stop.



**755nm**

More powerful energy absorption by the melanin chromophore, making it ideal for the widest range of hair types and color  
 - especially light-colored and thin hair

**808/810nm**

Deep penetration of the hair follicle with high average power with high repetition rate for fast treatment. moderate melanin absorption level making it safe for darker skin types.  
 ideal for treating the arms, legs, cheeks and beard.

**1064nm**


low melanin absorption, focused solution for darker skin types. Offers the deepest penetration of the hair follicle, embedded hair in areas as the scalp, armpit, and pubic area.

# Hair removal principle

Make Your Beauty Business More Easier



The laser selectively acts on the melanin in the hair follicle, destroying the hair-growing area






Natural hair loss, prevent regeneration, and achieve the purpose of hair removal



Hair removal also stimulates collagen regeneration, shrinks pores and makes skin firm and smooth

... ..  
 ... ..  
 ... ..



1

2


3

1. 12.4 : (1  
 6 (2 luanguage .  
 (3 LOGO  
 Before After  
 12.4 : (1  
 6 (2 luanguage .  
 (3 LOGO  
 Before After

12 1000 10 1200  
 12  
 40  
 Energy  
 10~150 j/cm2  
 40 ~ 800  
 Frequency  
 1 10  
 TEC 1200W  
 12 \* 20 35 \* 12  
 -10 3  
 AC220/110V 50/60HZ

12 1000 10 1200  
 12  
 40  
 Energy  
 10~150 j/cm2  
 40 ~ 800  
 Frequency  
 1 10  
 TEC 1200W  
 12 \* 20 35 \* 12  
 -10 3  
 AC220/110V 50/60HZ

## Custom Section



12 1000 10 1200

## OUR TEAM

There are more than 100 members of production team in our factory.



## OUR COUNTRIES

All the products are taking with CE/ISO certification ,suitable for world market , mainly used on North America , South America Europe 60. 000+ Customers Business development in 102+ countries...

mingliangkj:

Weifang Mingliang electronics Co., Ltd (MLKJ) 专业生产各种美容仪器 产品远销世界各地 深受客户好评

. 产品 种类 繁多

. 产品 质量 稳定 性能 卓越 售后服务 周到 欢迎 各界 人士 垂青 合作

本公司 為 您 提供 最 專業 的 服務 . 我們 有 豐富 的 經驗 和 專業 的 技術 人員 為 您 提供 最 專業 的 服務 . 我們 有 豐富 的 經驗 和 專業 的 技術 人員 為 您 提供 最 專業 的 服務 . 我們 有 豐富 的 經驗 和 專業 的 技術 人員 為 您 提供 最 專業 的 服務 .

1. Weifang Mingliangkj electronics Co., Ltd (電話: MLKJ) 15 . 我們 有 豐富 的 經驗 和 專業 的 技術 人員 為 您 提供 最 專業 的 服務 .  
 2. 我們 有 豐富 的 經驗 和 專業 的 技術 人員 為 您 提供 最 專業 的 服務 .  
 3. 我們 有 豐富 的 經驗 和 專業 的 技術 人員 為 您 提供 最 專業 的 服務 .

# PACKING

safe and thoughtful packaging service



**Tight packaging**  
 Training:  
 (video + manual + online service)  
 can keep you operate it easily

**Built-in prevention collision bubble**  
 Two- year warranty for machine handle as consumable, one-year warranty



**3-5 business days delivery**  
 professional guide:  
 24 hours professional online customer service