




STRONGER SMARTER FASTER


Laser painless hair removal
Triple waves: 755nm/808nm/1064nm
Suitable for all skin types



00000 00000000



0000 00000






Laser show Handle laser bar optional



④ 10bar

④ 12bar

④ 16bar



□□□□ □□□□□□ □□ □□ □□□

Suits for all skin and hair types



808nm

1064nm



- **755nm for white skin** (fine, golden hair removal)

● **808nm for yellow neutral skin** (brown hair removal)

- **1064nm for black skin** (black hair removal)




- 1.** _____ **15** _____.

2-□□□ □□□ □□□□ □□□ □ □□□□ □□□ □□ □□□□ □□□□ □□□□ □□□□.

3. 本公司對於 TEC 公司所屬之各項資產，並無任何權利或利益。

Treatment Comparison



00000 OEM

1. 000000 000 0 000
2. 00000000 0000 000000 00 0000000 0000 00000

customer visit



Packing

Safe and thoughtful packaging service



Tight packaging

The machine shall be made of waterproof materials and packaged

**Anti collision foam board
inside aluminum box**



3-5 business days delivery

Professional guide:

24 Hours Professional online customer service