



350g lightweight **handle**, more ergonomic

Available in **black or white**



1064 808 755 □□□□ □□□□ □□□□ □□□□ □□□□ □□□□□□

□□□ 1000 □□□□ 10 □□□□ □□□□ 20 * 12 □□□□ □□□□□□.

.000 1200 0000 12 0000 0000 35 * 12 0000 000000

□□□ 1600 □□□□ 16 □□□□ □□□□ 35 * 12 □□□□ □□□□□□.

□□□□ □□□□□□ □□□ □□□□□□ □□□□

□□ □□ □□□ □□□ □□□ □□□ □□ □ □□ □□□ □□□ □□□ □□ □□



0000 0000 0000 0 0000 00 0000 00 0000 00 0000




□□□□ □□□□

1. □□□□ □□□□ □□□□ 14 □□□ □□□ □□□□ □□□□
2. □□□□ □□□□ □□□□ □□□ □□□ □□□□ □□□□ □□□□

.3. OEM ()
 .4 OEM ()

The new 14-inch 4K screen

Support system customization



Technical Specifications

Wavelength	755nm808nm1064nm
Spot size	16 --- 8mm
Spot size	100mm
Spot size	14mm
Spot size	808nm808nm755nm1064nm
Spot size	12 * 35mm20 * 12 / 20mm
Spot size	808nm40000000-100000000nm
Spot size	10-150 J / cm2 150 J / cm2
Spot size	40 ~ 800 J / cm2
Spot size	1.0-10 J / cm2
Spot size	TEC TEC TEC TEC TEC
Spot size	800w/1000w/1200w/1600w
Spot size	2000 J / cm2
Spot size	220 J / cm2 60 / 110 J / cm2 50 / 110 J / cm2
Spot size	-10 ~ 3 J / cm2
Spot size	27 J / cm2 31 J / cm2
Spot size	AC220V/110V 50~60Hz

□□□□ □□ □□□□□ □ □□□□□ □□□□ □□□□□ □□□□!