

Diode laser

hair removal machine

Safe • Fast • Painless • permanent



sdqym.en.alibaba.com

Sync to machine

SMART CLING

Intelligent | Interconnected | Efficient



1. $\frac{\text{တစ်ခုခု} / \text{တစ်ခုခု တစ်ခုခု တစ်ခုခု} / \text{တစ်ခု နှင့် တစ်ခု တစ်ခု တစ်ခု တစ်ခုခု} / \text{တစ်ခု တစ်ခု တစ်ခုခု} / \text{တစ်ခုခုခု တစ်ခု တစ်ခုခုခုခုခု}$
တစ် တစ်ခု တစ်ခု
- တစ်ခုခုခု တစ် တစ်ခု .2
- တစ်ခုခု တစ်ခုခု တစ်ခုခုခု တစ်ခုခု တစ်ခုခုခု .3
- တစ် တစ်ခုခု .တစ်ခု တစ်ခုခု တစ်ခု တစ် တစ် တစ် တစ်ခုခုခုခုခု .4
- တစ်ခု တစ်ခုခု တစ်ခုခု တစ် တစ်ခုခုခု တစ်ခု တစ်ခုခု .5

Frequency	Pulse	Energy	Total	Date
5	30	78	0	2023-05-08 11:25:11
5	30	78	0	2023-05-08 11:25:13
5	30	78	0	2023-05-08 11:25:17
5	30	78	0	2023-05-08 11:25:19

Multimedia Control System

Supports Bluetooth /Wifi /Remote control and locking/Cloud storage



* 本系统支持蓝牙/WiFi/远程控制/锁定/云存储。

15.6" Smart Clinic Multimedia Monitor with HD 4K Screen



* 15.6" Smart Clinic Multimedia Monitor with HD 4K Screen. The monitor is designed for medical use and features a large, clear display for patient information and medical images.

* The monitor is compatible with various medical devices and software, making it a versatile tool for healthcare professionals. It also features a built-in speaker for audio output.

The monitor is available in two sizes: 15.6" and 18.5".

The monitor is made of high-quality materials and is designed to be durable and reliable. It also features a built-in speaker for audio output. The monitor is available in two sizes: 15.6" and 18.5". The price of the monitor is \$755 (nm808nm1064nm). The monitor is available in two sizes: 15.6" and 18.5".

350g
Ultra light handle

12x24 mm
Handle
1200W diode laser hair removal

12x36mm
Handle
1800W diode laser hair removal

0000 000 00 .0000000 0000000 000 0000 0 000000 0000000000
 0000000 000 000000 000000 0000 0000 0000000 000 000 000000
 00000 000000 000000 000 00000 00000 000000

LASER COMPARISON

【Other - Lasers】



- ✓ The original structure is not light enough.
- ✓ Big dimension.
- ✓ Short life.

【2022-MLKJ-Lasers】



- ♥ Lighter weight.
- ♥ Smaller dimension.
- ♥ More advanced structure design.
- ♥ More advanced performance.

【2022-MLKJ-Medical-Lasers】



- ♣ More advanced packaging technology.
- ♣ Higher energy densit.
- ♣ Lighter appearance.
- ♣ Longer life.

What can
we do
in
1 MINUTE

Time for a cup of instant coffee,
the handle can quickly frost.




EXFU[®]
Simple · Safe · Enjoy



sdqym.en.alibaba.com

Suitable for hair removal on any part of the body,
Such as arms, legs, face, armpits, back, chest, etc.



□□□□□ □□□ □□□□ □□□□ □□□□ □□□□ □□□□ □□□□.



IT'S TOO TO FAST

Easy to realize rental control,
Treatment data synchronization.



Android OS



Touch Screen



Built-in Speaker

□□□□□ □□□ □□□□□□ □□ □□□□□□ □□□□□□!