



New Style Diode Laser

Painless, permanent hair removal

..... 24

Diode Laser

For You. For Life.



0000 00000 00000 0000 000000 1064 808 755 0000

- 1) 00000000 00 TEC 24 00 000000 000 00 00000000 00 0000 000000 000000 000000 000000 0000 0000 000000 00000000 .0000 00 0000 00000000 00 0000 000000
- 00000 000000000 000000 0000 0000 400000000 0000000000 000000000 00000 00000 0000 00 (2
- .0000 0000000000 000000 000000 1 00000 00 000000 000000 1 00000000 2 (3
- 1600 00000 000000 000000 (4w 000000 00000000 00 0000 0000 0000 0000 00000 00000000.

350g lightweight **handle**, more ergonomic

Available in **black or white**



1064 808 755 □□□□ □□□□ □□□□ □□□□ □□□□□□

□□□ 1000 □□□□ 10 □□□□ □□□□ 20 * 12 □□□□ □□□□□□.

.000 1200 0000 12 0000 0000 35 * 12 0000 000000

1600 16 35 * 12

[illegible]

0000 000000 000 000000 00000



1064 808 755 1064nm 808nm 755nm 1064nm 808nm 755nm

- 1) 1064nm 808nm 755nm 1064nm 808nm 755nm
 - 2) 1064nm 808nm 755nm 1064nm 808nm 755nm
- 1064nm 808nm 755nm 1064nm 808nm 755nm 1064nm 808nm 755nm (3.



0000 0000 0000 0 0000 00 0000 00 0000 00 0000




□□□□ □□□□

1. □□□□ □□□□ □□□□ 14 □□□ □□□ □□□□ □□□□
2. □□□□ □□□□ □□□□ □□□ □□□ □□□□ □□□□ □□□□

.3 .
 OEM (/)

The new 14-inch 4K screen

Support system customization



Parameters

Wavelength	755nm808nm1064nm
Pulse width	16 --- 8ms
Spot size	100mm
Screen size	14inch
Wavelength	808nm808nm755nm1064nm
Spot size	12 * 35mm20 * 12 / mm2
Energy	808nm40000000-100000000J/cm2
Energy	10-150J / cm2 150mm2
Energy	40 ~ 800J/cm2
Energy	1.0-10J/cm2
Energy	TEC
Energy	800w/1000w/1200w/1600w
Energy	2000W
Energy	220V60 / 110V50 / Hz
Energy	-10 ~ 3mm
Energy	27mm31mm
Energy	AC220V/110V 50~60Hz

□□□□ □□ □□□□□ □ □□□□□ □□□□ □□□□□ □□□□!