

Diode Laser



15 Bar **1800W** Handle

*Increase the treatment head of nasal hair
and treat small parts easily



.00000 0000 000000 0000 0000000
00000 000 00 00000 000000 00000000 00000 *
00000 000 00 00000 000000 *
00000 0 00000 *
.00 000 0000000 000 000000 00000000000 *
808 000000 00000 0000 0000 *nm 7558081064 00nm.

350g
Ultra light handle



12×36mm

Handle

1800W diode laser hair removal




12×24 mm

Handle

1200W diode laser hair removal

이 제품은 다양한 파장 (755nm, 808nm, 1064nm)을 지원하는 다기능 레이저 탈모기입니다. 1064nm 파장은 깊은 피부층에 도달하여 모낭을 표적화하며, 808nm 파장은 모낭과 모근을 표적화하며, 755nm 파장은 표피층에 작용하여 모낭을 표적화합니다.

755nm (Alexandrite 레이저)는 표피층에 작용하여 모낭을 표적화하며, 808nm (Diode 레이저)는 모낭과 모근을 표적화하며, 1064nm (YAG 레이저)는 깊은 피부층에 도달하여 모낭을 표적화합니다.






ALEX 755nm
For white skin
(fine, golden hair removal)




SPEED 810nm
For yellow neutral skin
(brown hair removal)



YAG 1064nm
For black skin
(black hair removal)



Treatment Comparison





Emergency stop button

12 inch big screen quick touch easy operate

Diode laser handle

Vents

Plug