




□□□□□


1.3 Waves Yag 1064nm Diode 808nm Alex 755nm □ 3 □□□ □□□□□□ □□□□ □□□□ □□□ □□□ 1 □□
 1000 □□□□ □□□□ :□□□□ □□□□W/1200W/1600W □□ □□□□ □□□□
 !□□□ □ □□□□ □□□□ □□□□ □□□□ □□□□ □□□□ □□□□ 38 * 12 □□□□ □□□□ 20 * 12 □□□□ □□□□ □□□□□□ .2
 □□□□ □□ □□□□□ □□□□□ □□□ □□□□□ □□□□□ □□□□□ □□□□□ □□□□□ □□□□□ □□□□□ □□□□□
 .□□□□ □□□□ □□□□ □□□□ 24 □□□□ □□□ □□□□ □□ □□□□□□ □□□□
 □□□□□□ □□□□□ □□ □□□□□□□□ □□□□□ :□□□□ □□□□.4



A natural



B energy absorbed by hair



C hair follicle died

Speed Diode 808nm 755nm 1064nm

Speed Diode 808nm 755nm 1064nm

Speed Diode 808nm 755nm 1064nm

Long Pulse 1064nm 755nm 808nm


Handle Details

Three Wavelengths Work Togher




12*20nm

755nm Laser
808nm Laser
1064nm Laser



12*35nm

755nm Laser
808nm Laser
1064nm Laser



□□□□□ □□□□ □ □□ □□□□□

1. □□□□□□□ □□□□ □□□□ :□□□□ □□□□ US Coherent/ Dilas brand2. 3 808 □□□□□□□ 755 :□□□□
1 □□ 3 □□□□□□□ 1064 □□□□□□□□
- □□□□ 35 * 12 □□□□ □□□□ 20 * 12 :□□□□ □□□□□□ .3
4. 1000 □□□□ □□□□ :□□□□W 1200W 1600W □ OEM
3. □□□ □□□□□ □□□□ 24 □□□□□□□ 1 □□ □□□□ □□ □□ □□□□ □□□□□□ □□□ □□□□□ □□□ :□□□□□□ □□□□



Super TEC. 22- 1

Super TEC. 22- 1

Before and After

Treatment comparison



Super TEC. 22- 1

1. Super TEC. 22- 1

Custom Section

CASE design



LOGO design



SYSTEM design



CERTIFICATE DISPLAY

